



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



8824GNK 8X8X24 SC Wireway 3

Unity MFG

Catalog Number	8824GNK
Manufacturer	Unity MFG
Description	Unity 8824GNK Lay-In Wireway, Removable Hinged Cover Type, Length: 24 In, Width: 8 In, 8 In Height, Nema 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 14 Ga Low Carbon Steel, Gunsmoke Gray Powder Coated, No Knockouts, C/Us UI 50 and UI 870 - Type 1: Intended For Indoor Use Primarily to Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, Csa C22.2 No. 26 Certified, Type 1, IEC 60529, Rohs Compliant, For Cable and Wire Junction, Distribution and Termination, H
Weight per unit	13.0 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

Cover Type	Removable Hinged
Knockouts	NO
Material	Low-Carbon Steel

Material, Color, and Finish

Finish	Powder Coat
--------	-------------

Dimensions and Weight

Height	8
Length	24
Width	8



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	Formed From Code Gauge, Low Carbon Steel
Description	8X8X24 SC WIREWAY 3
extra long description	UNT 8824GNK N1 HINGED COVER WIREWAY
Long Description	Unity 8824GNK Lay-In Wireway, Removable Hinged Cover Type, Length: 24 IN, Width: 8 IN, 8 IN Height, NEMA 1, IP30 Enclosure, Construction: Formed From Code Gauge, Low Carbon Steel, 14 GA Low Carbon Steel, Gunsmoke Gray Powder Coated, No Knockouts, C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC 60529, RoHS Compliant, For Cable And Wire Junction, Distribution And Termination, H
Product Type	N1 Hinged Cover Wireway No K.O. Powder Coated
Special Features	For protecting electrical wiring where dust, dirt, oil and water are not serious problems; All sections and fittings are fully open on one side so wires and cables can be laid in along an entire run; No pulling-through of wires or cables is required; Wireway body has mounting holes on the back; Cover is secured to the body with plated screws; Keyhole slots are furnished on the wireway cover which allow easy access to the inside without removing the screws; #10-32 x 5/16 thread forming screw

Manufacturer Information

Brand	Unity
GTIN	00761515104200
Manufacturers Part Number	8824GNK
UPC	761515104200

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Lay-In Wireway

Packaging

Carton	1
Weight Per each	13



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Cable And Wire Junction, Distribution And Termination,
Houses Runs Of Control And Power Cable

Enclosure
standard

NEMA 1, IP30

C/US UL 50 And UL 870 - Type 1: Intended For Indoor Use
Primarily To Provide A Degree Of Protection Against Limited
Amounts Of Falling Dirt, CSA C22.2 No. 26 Certified, Type 1, IEC
60529, RoHS Compliant