



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



885TRGCC12 Radiant 15A/125V TR Dup Recp GRP CC12

Pass & Seymour/Legrand

Catalog Number	885TRGCC12
Manufacturer	Pass & Seymour/Legrand
Description	15A/125V Tamper-Resistant Receptacle, Graphite
Weight per unit	0.1100 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

indoor/outdoor	Indoor
Mounting Type	Box
Outlet Type	Tamper-Resistant, Indoor, Residential
Poles	Double Pole
Voltage	125.0 V

Descriptions

Description	RADIANT 15A/125V TR DUP RECP GRP CC12
extra long description	P&S 885TRGCC12 RADIANT 15A/125V TR
Long Description	15A/125V Tamper-Resistant Receptacle, Graphite
Product Type	Radiant 15A/125V TR Dup Recp GRP CC12

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007173710
Manufacturers Part Number	885TRGCC12
UPC	785007173710

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	12
Weight Per each	0.11

Uses, Certifications, and Standards

environmental conditions	95% (relative humidity, non-condensing)
nema rating	15A
standard	CULUS, UL