

TYPE 1 ENCLOSURES



Screw Cover – Powder Coated

- Designed for use as junction and pull boxes
- Stock inventory sizes from 4x4x4 to 48x48x18
- Custom sizes and modifications available

SPECIFICATIONS

- Manufactured from code gauge, low carbon steel
- Covers feature keyhole slots which allow the plated screws to stay in place and make for easy installation
- Embossed grounding provision on sizes up to 24x24x12
- Holes are incorporated into the back of enclosure for easy mounting
- Available with or without knockouts

FINISH

- Standard: Gunsmoke Gray Powder Coated
- Optional powder coat colors and custom silkscreen printing available (see pg. 48)

INDUSTRY STANDARDS

- Type 1 - UL 50 and UL 50E: Intended for indoor use primarily to provide a degree of protection against limited amounts of falling dirt.
- RoHS compliant

ACCESSORIES



Replacement Screw Cover Lid – Powder Coated



Flush Cover Lid – Powder Coated

CATALOG NUMBER	UPC (761515)	SIZE (W"xH"xD")	WGT	SCREW COVER	FLUSH COVER
444SC	22010	4x4x4	1	44SC	44FC
664SC	22130	6x6x4	3	66SC	66FC
666SC	22140	6x6x6	3	66SC	66FC
684SC	22160	6x8x4	3	68SC	68FC
6124SC	22166	6x12x4	5	612SC	612FC
884SC	22280	8x8x4	4	88SC	88FC
886SC	22290	8x8x6	5	88SC	88FC
8104SC	22320	8x10x4	5	810SC	810FC
8124SC	22360	8x12x4	6	812SC	812FC
10104SC	22430	10x10x4	6	1010SC	1010FC
10106SC	22440	10x10x6	7	1010SC	1010FC
12124SC	22580	12x12x4	8	1212SC	1212FC
12126SC	22590	12x12x6	10	1212SC	1212FC
12184SC	22700	12x18x4	11	1218SC	1218FC
12186SC	22710	12x18x6	14	1218SC	1218FC
CATALOG NUMBER	UPC (761515)	SIZE (W"xH"xD")	WGT	SCREW COVER	FLUSH COVER
444SCNK	22012	4x4x4	1	44SC	44FC
664SCNK	22132	6x6x4	3	66SC	66FC
666SCNK	22142	6x6x6	3	66SC	66FC
884SCNK	22282	8x8x4	4	88SC	88FC
886SCNK	22292	8x8x6	5	88SC	88FC
888SCNK	22300	8x8x8	6	88SC	88FC
10104SCNK	22432	10x10x4	6	1010SC	1010FC
10106SCNK	22442	10x10x6	7	1010SC	1010FC
12124SCNK	22582	12x12x4	8	1212SC	1212FC
12126SCNK	22592	12x12x6	10	1212SC	1212FC
12128SCNK	22600	12x12x8	11	1212SC	1212FC
121210SCNK	22610	12x12x10	13	1212SC	1212FC
121212SCNK	22620	12x12x12	15	1212SC	1212FC
16164SCNK	22940	16x16x4	12	1616SC	1616FC
16166SCNK	22950	16x16x6	14	1616SC	1616FC
18184SCNK	23020	18x18x4	16	1818SC	1818FC
18186SCNK	23030	18x18x6	19	1818SC	1818FC
18188SCNK	23040	18x18x8	20	1818SC	1818FC
181810SCNK	23050	18x18x10	23	1818SC	1818FC
181812SCNK	23060	18x18x12	25	1818SC	1818FC
18246SCNK	23100	18x24x6	24	1824SC	1824FC
24244SCNK	23290	24x24x4	27	2424SC	2424FC
24246SCNK	23300	24x24x6	30	2424SC	2424FC
24248SCNK	23310	24x24x8	34	2424SC	2424FC
242410SCNK	23320	24x24x10	38	2424SC	2424FC
242412SCNK	23330	24x24x12	44	2424SC	2424FC
30306SCNK	23340	30x30x6	45	3030SC	3030FC
30308SCNK	23480	30x30x8	51	3030SC	3030FC
303010SCNK	23530	30x30x10	55	3030SC	3030FC
303012SCNK	23580	30x30x12	65	3030SC	3030FC
36366SCNK	23440	36x36x6	60	3636SC	3636FC
36368SCNK	23500	36x36x8	78	3636SC	3636FC
363610SCNK	23550	36x36x10	79	3636SC	3636FC
363612SCNK	23600	36x36x12	87	3636SC	3636FC
363618SCNK	23602	36x36x18	150	3636SC	3636FC
48488SCNK	23505	48x48x8	195	4848SC	n/a
484812SCNK	23605	48x48x12	220	4848SC	n/a
484818SCNK	23610	48x48x18	276	4848SC	n/a

WITH KNOCK-OUTS

WITHOUT KNOCK-OUTS

TYPE 1 ENCLOSURES

TYPE 3 AND 3R ENCLOSURES

CABLE MANAGEMENT SOLUTIONS

UTILITY AND STORAGE CABINETS

HARDWARE AND ACCESSORIES

CUSTOM ENCLOSURE SOLUTIONS

