



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 89045 Omniconn RG-6 Quad F Comp Conn Black, 50/Jar

*Ideal*

|                  |  |
|------------------|--|
| Catalog Number   | 89045  |
| Manufacturer     | Ideal  |
| Description      | Ideal, Compression Connector, Omniconn, F-Type, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 Ohm, Ports Size: 7/16 In, Coaxial Cable Type: RG-6, Bandwidth: 3 GHZ, Dielectric Diameter: 0.175 - 0.183 In, Overall Jacket Diameter: 0.260 - 0.280 In |
| Weight per unit  | 0.0190 (lbs/each)  |
| Product Category | Coaxial & Twinaxial Connectors   |

### Features

|          |       |
|----------|-------|
| Material | Brass |
|----------|-------|

### Material, Color, and Finish

|        |               |
|--------|---------------|
| Finish | Nickel-Plated |
|--------|---------------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | OMNICONN RG-6 QUAD F COMP CONN BLACK, 50/JAR  |
| extra long description | IDEAL 89-045 RG6 QUAD COMPR CONN,OM   |
| Features               | Connector Model: 6QFOCAccepts RG-6 Quad coax cablesCenter conductor range: AllDielectric diameter range: .175" - .183"Outer jacket diameter range: .270" - .295"Recommended cable prep/stripping tools: 45-605 PrepPRO; 45-526Recommended compression tools: 30-793 OmniSeal PRO XL; 33-632 Linear X3The IDEAL OmniConn F connector is a cable specific connector solution for RG-6 coax. The OmniConn connectors have a combination brass and plastic exterior and an inner O-ring to provide a weather proof connection suita |
| Long Description       | IDEAL, Compression Connector, OmniCONN, F-Type, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 OHM, Ports Size: 7/16 IN, Coaxial Cable Type: RG-6, Bandwidth: 3 GHZ, Dielectric Diameter: 0.175 - 0.183 IN, Overall Jacket Diameter: 0.260 - 0.280 IN  |
| Product Type           | RG6 Quad Compr Conn, Omni, 50JR   |
| Special Features       | Features: OmniCONN F compression connectors install easily onto standard RG 6 and RG 6Quad cables; Non corrosive nickel plated brass body and polycarbonate bushing; Delrin/Nylon adapter sleeve and o-ring provide double protection for a watertight seal; Free spinning hex nut for ease of installation onto all 7/16 IN ports 75 OHM nominal impedance; Bandwidth up to 3 GHZ; Nominal Impedance: 75 OHM; Ports Size: 7/16 IN; Coaxial Cable Type: RG-6; Bandwidth: 3 GHZ; Dielectric Diameter: 0.175 - 0.183 IN; Overall  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250890453 |
| Manufacturers Part Number | 89-045         |
| UPC                       | 783250890453   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
| Type                 | F-Type                                 |

## Availability

|             |    |
|-------------|----|
| minimum qty | 50 |
|-------------|----|

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 50    |
| Weight Per each | 0.019 |

## Uses, Certifications, and Standards

|             |   |
|-------------|---|
| Application | Terminating an F Style connection onto RG 6 Quad Coax . |
|-------------|---|