



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



89049 Insite RG-59 Plenum BNC Compression Conn, 15/Card

Ideal

Catalog Number	89049
Manufacturer	Ideal
Description	Ideal, Compression Connector, BNC, Conductor Range: 029 - 042 In, 20 - 18 Awg Solid Center Conductor, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 Ohm, Dielectric Diameter: 0.130 - 0.141 In, Coaxial Cable Type: RG-59 Plenum, Overall Jacket Diameter: 0.188 - 0.230 In
Weight per unit	0.0400 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

Material	Brass
----------	-------

Material, Color, and Finish

Finish	Nickel-Plated
--------	---------------

Descriptions

Description	INSITE RG-59 PLENUM BNC COMPRESSION CONN, 15/CARD
extra long description	IDEAL 89-049 RG59 PLENM INSITE BNC
Features	Connector Model: 59PLBNCISAccepts RG-59 plenum coaxCenter conductor range: 23-18 AWG Solid (.023" - .040")Dielectric diameter range: .134" - .140"Outer jacket diameter range: .193" - .224"Recommended cable prep/stripping tools: 45-605 PrepPRORecommended compression tools: 30-793 OmniSeal PRO XL; 33-632 Linear X3Installing one-piece compression BNC and right angle connectors just got easier. No more uncertainty when inserting the cable into the connector. No more collapsed center pins. No more wasted connec
Long Description	IDEAL, Compression Connector, BNC, Conductor Range: 029 - 042 IN, 20 - 18 AWG Solid Center Conductor, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 OHM, Dielectric Diameter: 0.130 - 0.141 IN, Coaxial Cable Type: RG-59 Plenum, Overall Jacket Diameter: 0.188 - 0.230 IN
Product Type	RG59 Plenm Insite BNC Con 15CD
Special Features	Features: Designed For CCTV System Installations/Integrations And General Purpose Applications; RG-6 And RG-59 Versions. 2 Connectors To Cover Most Plenum Rated Coax Cables Available In The Market; Compression Sleeve Adapts To A Wide Range Of Outer Jacket Cable Diameters; Solid All-Brass Construction For Permanent Installations; Gold Plated Contact Pin And Mating Area; Color Bands For Cable Series Identification; Nickel-Plated, Brass-Construction For Superior Corrosion Resistance; Moisture-Inhibiting Desig



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Ideal
GTIN	00783250890491
Manufacturers Part Number	89-049
UPC	783250890491

Taxonomies, Classifications, and Categories

Category Description	Residential cord connectors
Type	BNC

Packaging

Carton	1
Package	15
Weight Per each	0.04

Uses, Certifications, and Standards

Application	For CCTV System Installations/Integrations And General Purpose Applications on RG 59 Plenum Cable
-------------	---