

Square Junction Boxes	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	16.0	9339-Z+1	"Z" hanger, flush with face of plaster ring, wire clamps - bulk packed	1-¼	4-¼	4-¼	10314	50	22
	16.0	9339-Z+1C2	"Z" hanger, flush with face of plaster ring, 2 wire clamps - factory installed	1-¼	4-¼	4-¼	10318	50	23
	27.3	9342-C2	Bottom mount, 2 wire clamps - factory installed	2-¼	4	4	10346	50	25
	27.3	9342-HF	Nail-on "HF" hanger, wire clamps - bulk packed	2-¼	4	4	10348	50	30
	27.3	9342-HN	Nail-on "HN" hanger, wire clamps - bulk packed	2-¼	4	4	10342	50	32
	32.3	9343-N	Nails, Speed Klamps™ - bulk packed	2-½	4-1/16	4-1/16	10370	50	26
	32.3	9343-NC2	Nails, 2 wire clamps - factory installed	2-½	4-1/16	4-1/16	57150	50	27
	32.3	9343-NK	Nails, Speed Klamps™ - factory installed	2-½	4-1/16	4-1/16	10374	50	27
	32.3	9343-SS	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, Speed Klamps™ - bulk packed	2-½	4-1/16	4-1/16	10375	50	27
	32.3	9343-SSK	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, Speed Klamps™ - factory installed	2-½	4-1/16	4-1/16	10376	50	27

Range/Dryer Receptacle	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	42.0	RD-42	Fetter ring nails, internal wire clamp - factory installed, knockout	3-13/16	4	3-¾	12907	24	22
	42.0	RD-42SS	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, internal wire clamp - factory installed, knockout	3-13/16	4	3-¾	12905	24	22

For use with 2-position devices; knockout accomodates #8 and #6 gauge wire.




Plaster Rings & Covers	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	—	9315	Round blank cover	—	4-¾ dia.	—	10130	100	16
	—	9315-WH	Round blank cover, white	—	4-¾ dia.	—	10132	100	16
	—	9344	Square blank cover; *Use with series 9339, 9342, and 9343 only	—	4	4	10360	100	15
	4.2	9345	Single gang plaster ring, thermoplastic material, ½" offset	5/8	4	4	10361	100	8
	5.1	9345-58	Single gang plaster ring, thermoplastic material, 5/8" offset; *Use with series 9339, 9342, and 9343 only	¾	4	4	10372	50	5
	6.7	9346	Two-gang plaster ring, thermoplastic material, ½" offset	5/8	4	4	10362	50	4
	8.1	9346-58	Two-gang plaster ring, thermoplastic material, 5/8" offset; *Use with series 9339, 9342, and 9343 only	¾	4	4	10390	50	4
	4.8	9347	Square plaster ring, reduces to 3/0 outlet, ½" offset; *Use with series 9339, 9342, and 9343 only	11/16	4-1/16	4-1/16	10386	50	8
	4.3	9348	Round plaster ring, reduces 4" dia. outlet box to 3" dia. opening, ½" offset; *Use with series 9350, 9351, 9364 and 9365 only	5/8	4 dia.	—	10366	100	11

All dimensions are in inches unless otherwise noted.
See page 7 for Attachment Coding suffix descriptions.



UL File No. E30594



Square Junction Boxes	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	16.0	9339-Z+1	"Z" hanger, flush with face of plaster ring, wire clamps - bulk packed	1-1/4	4-1/4	4-1/4	10314	50	22
	16.0	9339-Z+1C2	"Z" hanger, flush with face of plaster ring, 2 wire clamps - factory installed	1-1/4	4-1/4	4-1/4	10318	50	23
	27.3	9342-C2	Bottom mount, 2 wire clamps - factory installed	2-1/4	4	4	10346	50	25
	27.3	9342-HF	Nail-on "HF" hanger, wire clamps - bulk packed	2-1/4	4	4	10348	50	30
	27.3	9342-HN	Nail-on "HN" hanger, wire clamps - bulk packed	2-1/4	4	4	10342	50	32
	32.3	9343-N	Nails, Speed Klamps™ - bulk packed	2-1/2	4-1/16	4-1/16	10370	50	26
	32.3	9343-NC2	Nails, 2 wire clamps - factory installed	2-1/2	4-1/16	4-1/16	57150	50	27
	32.3	9343-NK	Nails, Speed Klamps™ - factory installed	2-1/2	4-1/16	4-1/16	10374	50	27
	32.3	9343-SS	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, Speed Klamps™ - bulk packed	2-1/2	4-1/16	4-1/16	10375	50	27
	32.3	9343-SSK	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, Speed Klamps™ - factory installed	2-1/2	4-1/16	4-1/16	10376	50	27

Range/Dryer Receptacle	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	42.0	RD-42	Fetter ring nails, internal wire clamp - factory installed, knockout	3-13/16	4	3-3/4	12907	24	22
	42.0	RD-42SS	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, internal wire clamp - factory installed, knockout	3-13/16	4	3-3/4	12905	24	22

For use with 2-position devices; knockout accomodates #8 and #6 gauge wire.



Plaster Rings & Covers	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	—	9315	Round blank cover	—	4-3/4 dia.	—	10130	100	16
	—	9315-WH	Round blank cover, white	—	4-3/4 dia.	—	10132	100	16
	—	9344	Square blank cover; *Use with series 9339, 9342, and 9343 only	—	4	4	10360	100	15
	4.2	9345	Single gang plaster ring, thermoplastic material, 1/2" offset	5/8	4	4	10361	100	8
	5.1	9345-58	Single gang plaster ring, thermoplastic material, 5/8" offset; *Use with series 9339, 9342, and 9343 only	3/4	4	4	10372	50	5
	6.7	9346	Two-gang plaster ring, thermoplastic material, 1/2" offset	5/8	4	4	10362	50	4
	8.1	9346-58	Two-gang plaster ring, thermoplastic material, 5/8" offset; *Use with series 9339, 9342, and 9343 only	3/4	4	4	10390	50	4
	4.8	9347	Square plaster ring, reduces to 3/0 outlet, 1/2" offset; *Use with series 9339, 9342, and 9343 only	11/16	4-1/16	4-1/16	10386	50	8
	4.3	9348	Round plaster ring, reduces 4" dia. outlet box to 3" dia. opening, 1/2" offset; *Use with series 9350, 9351, 9364 and 9365 only	5/8	4 dia.	—	10366	100	11

All dimensions are in inches unless otherwise noted. See page 7 for Attachment Coding suffix descriptions.



UL File No. E30594