

# fiberglass BOX™ Fan & Fixture Support

## 3-½" & 4" Fan/Fixture Support Box



3-½" Dia.	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fan Rating	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W					
	16.0	9336-NKFR	3-½" diameter fan & fixture support, side fetter ring nail mount, Speed Klamps™ - factory installed	2-3/8	3-½	35 lb.	50 lb.	10305	50	23
	20.5	9335-NFR	3-½" diameter fan & fixture support, side fetter ring nail mount, Speed Klamps™ - bulk packed	2-7/8	3-½	35 lb.	50 lb.	41201	50	25
	20.5	9335-NKFR	3-½" diameter fan & fixture support, side fetter ring nail mount, Speed Klamps™ - factory installed	2-7/8	3-½	35 lb.	50 lb.	41202	50	25

4" Diameter Fan & Fixture Support	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fan Rating	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W					
	8.0	9370-FR	4" diameter pan fan box, ½" deep base, "pop-in" cable clamp, mounting hardware included	1-½ overall	4	70 lb.	110 lb.	76600	24	6
	14.0	9375-FR	4" diameter thermoplastic fan box, ½" deep base, Speed Klamps™ - molded in, two ½" knockouts, mounting hardware included	3-13/16 overall	4	70 lb.	110 lb.	79291	24	7
	15.0	9364-FANB	4" diameter fan box, adjustable bar hanger, Speed Klamps™ - factory installed	1-11/16	4	35 lb.	50 lb.	99025	20	39
	15.0	9364-KFR	4" diameter bottom mount, Speed Klamps™ - factory installed, mounting hardware included	1-11/16	4	35 lb.	50 lb.	10620	50	21
	15.0	9365-NKFR	4" diameter fan & fixture support, side fetter ring nail mount, "HL" hanger, Speed Klamps™ - factory installed	1-11/16	4	35 lb.	50 lb.	75392	50	29
	16.0	9369-FB	4" diameter fan & fixture support, surface mount, Speed Klamps™ - factory installed, mounting hardware included	1-¾	4	35 lb.	50 lb.	76500	25	12
	16.0	9369-FBH	4" diameter fan box, side mount hanger, Speed Klamps™ - factory installed, mounting hardware included	1-¾	4	35 lb.	50 lb.	76501	25	18
	16.0	9369-FRBKB	4" diameter fan box, adjustable bar hanger, Speed Klamps™ - factory installed	1-¾	4	70 lb.	125 lb.	99739	20	28
	16.5	9373-FR	4" diameter thermoplastic fan box, ½" deep base, Speed Klamps™ - molded in, mounting hardware included	6 overall	4	70 lb.	110 lb.	78254	40	16
	22.5	9350-FANB	4" diameter fan box, adjustable bar hanger, Speed Klamps™ - factory installed, bulk packed	2-7/16	4	35 lb.	50 lb.	99021	20	32
	22.5	9350-KFR	4" diameter bottom mount, Speed Klamps™ - factory installed, mounting hardware included	2-7/16	4	35 lb.	50 lb.	10459	50	24
	22.5	9351-NFR	4" diameter fan & fixture support, side fetter ring nail mount, Speed Klamps™ - factory installed	2-7/16	4	35 lb.	50 lb.	65001	50	27
	22.5	9351-NKFR	4" diameter fan & fixture support, side fetter ring nail mount, Speed Klamps™ - factory installed	2-7/16	4	35 lb.	50 lb.	65002	50	28



All dimensions are in inches unless otherwise noted.  
See page 7 for Attachment Coding suffix descriptions.

Old Work/Manufactured Housing Boxes

Outlet Box  
UL File No. E30594