



DRAFT-BLOCK™

Expanding Polyurethane Foam

[Description](#) | [Characteristics](#) | [Applications](#) | [Packaging](#) | [Instructions](#) | [Precautions](#) | [Specifications](#) | [Limited Warranty](#)

DESCRIPTION:

Draft-Block™ is a one component expanding polyurethane foam sealant. It is designed to be dispensed as a bead from its aerosol container to fill voids, cracks, crevices and small cavities on flat or irregular surfaces.

When cured, Draft-Block™ is an odorless, non-corrosive, non-reactive inert substance which contains no ureaformaldehyde.

[Top of Page](#)

CHARACTERISTICS:

- Reduces heating and cooling costs by filling and insulating openings
 - Reduces sound transmission - an effective acoustical sealant.
 - Tack-free approximately 45 minutes after being dispensed, cures to a firm resiliency in about 8 hours at 50% relative humidity
 - Totally dielectric - will not transmit an electric current
 - Adheres readily to wood, glass, metal, tile, concrete and most plastics
 - Expands to three times its original dispensed. R-factor of 5 at 1 inch thickness

[Top of Page](#)

APPLICATIONS:

RectorSeal® Draft-Block™ is an excellent filler which bonds and insulates.

Use in voids around plumbing and utility penetrations to stop drafts and prevent the intrusion of insects and other pests.

Seal around windows, air conditioners, ducts and vents. Stops air leakage while filling cracks and voids. An energy saver in both heating and cooling seasons.

Seal voids in siding, door jams, foundation, and concrete joints, is resistant to water and outdoor exposure.

[Top of Page](#)

PACKAGING:

Code	Size	Qty. Per Case	Lbs. per Case	Cu. Ft Per Case
96500	12 oz. Aerosol can	12 cans	13	0.56

[Top of Page](#)

INSTRUCTIONS:

-
1. Screw trigger/ straw onto valve.
 2. Shake can vigorously for at least one minute before use.
 3. Hold can UPSIDE DOWN, slowly activate trigger until foam flows smoothly. Never activate valve with can right side up as propellant will escape. Practice on a piece of newspaper. Fill cavities only 33% full.
 4. Clean uncured foam IMMEDIATELY with paint thinner, acetone, or nail polish remover with acetone. Cured foam cannot be removed with solvents. For foam which hardens on skin, soak affected area in warm soapy water, then apply petroleum jelly. Foam will wear off in time. Cured foam is not harmful to health from skin contact.

For additional technical information, call Toll Free 1-800-231-3345.

[Top of Page](#)

PRECAUTIONS:

FOR CHEMICAL EMERGENCY, SPILL, LEAK, FIRE, EXPOSURE OR ACCIDENT,

CALL CHEMTREC - DAY OR NIGHT 1-800-424-9300

CAUTION!

COMBUSTIBLE

Store Draft-Block™ at temperatures between 32 degree F - 90 degree F (0 degree C- 32 degree C). this product is **FLAMMABLE DURING DISPENSING**. Shut off all gas pilot lights, electrical igniters, and other sources of ignition before and during use. **DO NOT** smoke or use matches or lighter while dispensing foam. Wear gloves and eye protection. Use only with adequate ventilation. Protect area with cloth or newspaper.

For additional information, refer to Material Safety Data Sheet.

[Top of Page](#)

SPECIFICATIONS:

Wt./Gal. @ 77 degree F	-156 degree F (-104 degree C) during dispensing
Color	Beige
Shelf Life	2 years, Subject to inspection
Federal Specification	HUD Section 507-6
ASHRAE 90-75	Section 45.4

R-13919 UNDERWRITERS LABORATORIES INC® CLASSIFIED CAULKINGS AND SEALANTS
SURFACE BURNING CHARACTERISTICS APPLIED TO INORGANIC REINFORCED CEMENT BOARD +
FLAME SPREAD: 25 SMOKE DEVELOPED: 50 39P2

Suggestions and recommendations covering the use of our products are based on our past experience and laboratory findings. However, as we have no control as to the methods and conditions of application, we only assume responsibility for the uniformity of our products within manufacturing tolerances.

[Top of Page](#)

LIMITED WARRANTY:

RectorSeal® makes the Limited Express Warranty that when the instructions for storage and handling of our products are followed we warrant our products to be free from defects. THIS LIMITED EXPRESS WARRANTY IS EXPRESSLY IN LIEU OF ANY OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, AND OF ANY OTHER OBLIGATION ON THE PART OF RECTORSEAL®. The sole remedy for breach of the Limited Express Warranty shall be the refund of the purchase price. All other liability is negated and disclaimed, and RectorSeal® shall not be liable for incidental or consequential damages.

[Top of Page](#)

RectorSeal®

2601 Spenwick Drive • Houston, TX 77055 USA

713-263-8001 • Fax 713-263-7577

Toll-free 800-231-3345 • Fax 800-441-0051

E-09

[Back to Other Related Products](#)