



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A174T300 Arealights 44065.4 Lumens A17 Type Iv 300W Led 120

Rab Lighting

Catalog Number	A174T300
Manufacturer	Rab Lighting
Description	Arealights 44065.4 Lumens A17 Type Iv 300W Led 120V-277V Pole Mount Bronze
Weight per unit	18.3 (lbs/each)
Product Category	Lighting

Features

amperage rating	2.40A/1.91A/1.59A @120V 1.37A/1.10A/0.92A @208V 1.24A/0.99A/0.83A @240V 1.05A/0.89A/0.74A @277V
average life	100000
Fixture Type	Suitable for wet locations
lumens	44065.4
Shape	Rectangular
Voltage Rating	120/277
Wattage	300

Material, Color, and Finish

Color	Bronze
-------	--------

Descriptions

Description	AREALIGHTS 44065.4 LUMENS A17 TYPE IV 300W LED 120
extra long description	RAB A17-4T300 Area A17 T4 300W LED
Long Description	Arealights 44065.4 Lumens A17 Type Iv 300W Led 120V-277V Pole Mount Bronze
Product Type	Area A17 T4 300W Led BZ
Special Features	Selectable wattage/CCT

Manufacturer Information

Brand	RAB Lighting Inc
GTIN	00192552003520
Manufacturers Part Number	A17-4T300
UPC	192552003520

Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
Type	AREA LIGHT

Packaging

Carton	1
Weight Per each	18.25

Uses, Certifications, and Standards

Application	Outdoor
Mounting	Universal Pole Mount