

Eaton A200M2CACD

Catalog Number: A200M2CACD

Eaton Freedom NEMA motor control starter, Non-Reversing Starter, 45A, Three-pole, Size 2, 7-1/2 hp at 115V, 10 hp at 208V, 15 hp at 240V, 25 hp at 480,600V, A200 series, Wired for Separate Control, Ambient Compensated Overload Relay



General specifications

| | |
|-------------------------------|--|
| Product Name | Catalog Number |
| Eaton A200 NEMA motor control | A200M2CACD |
| UPC | Product Length/Depth |
| 786678232485 | 4.94 in |
| Product Height | Product Width |
| 3.31 in | 4.38 in |
| Product Weight | Warranty |
| 3.3 lb | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| Certifications | Catalog Notes |
| UL Listed CSA Certified | For ambient compensated overload relay with auto-reset, add Suffix D. |

Accessories

Motor control

Phase

Three-phase magnetic

Size

2

Amperage rating

45A

Series

A200

HP rating - max

7-1/2 hp at 115V, 10 hp at 208V, 15 hp at 240V, 25 hp at 480,600V

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Installation instructions

[Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)

Specifications and datasheets

[Eaton Specification Sheet - A200M2CACD](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)