



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A224T200 Area Light Led 27K LM Pole MT

Rab Lighting

Catalog Number	A224T200
Manufacturer	Rab Lighting
Description	A22 Area Light 200/180/160W 3000/4000/5000K Type Iv Pole Mount 7PRS Bronze
Weight per unit	13.0 (lbs/each)
Product Category	Lighting

Features

amperage rating	1.67A/1.50A/1.33A @120V 0.96A/0.87A/0.77A @208V 0.83A/0.75A/0.67A @240V 0.72A/0.65A/0.58A @277V
average life	100000
Fixture Type	Suitable for wet locations. Suitable for mounting within 4ft (1.2m) of the ground.
lumens	21,262-27,463
Voltage Rating	120-277
Wattage	155.1-200.5

Descriptions

Description	AREA LIGHT LED 27K LM POLE MT
extra long description	RAB A22-4T200 A22 200/180/160 4T 3/
Long Description	A22 AREA LIGHT 200/180/160W 3000/4000/5000K TYPE IV POLE MOUNT 7PRS BRONZE
Product Type	A22 200/180/160 4T 3/4/5K Pole 7PRS BZ
Special Features	Selectable wattage/CCT

Manufacturer Information

Brand	RAB Lighting Inc
GTIN	00192552035385
Manufacturers Part Number	A22-4T200
UPC	192552035385

Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
Type	AREALIGHTS

Packaging

Carton	1
Weight Per each	13

Uses, Certifications, and Standards

Application	Outdoor
Mounting	Universal Pole Mount