



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A24H2408GQRLP3PT 24.19X24.19X8 N4X FG 3PT LTCH HC *Hoffman Enclosures, Inc.*

Catalog Number	A24H2408GQRLP3PT
Manufacturer	Hoffman Enclosures, Inc.
Description	Hinge Cover Enclosure 3-Point Type 4X, 24.19X24.19X8.00, Gray, Fiberglass
Weight per unit	32.0 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

Features

ip rating	IP66
Material	Fiberglass

Material, Color, and Finish

Color	Gray
Finish	Smooth Matte

Dimensions and Weight

Depth	8
Height	24.19
Size	24.19x24.19x8.00 in
Width	24.19

Descriptions

Description	24.19X24.19X8 N4X FG 3PT LTCH HC
extra long description	NVENT HOF A24H2408GQRLP3PT FG WALL
Features	A full range of modification options are available for wall-mount fiberglass enclosures, including variable depths to accommodate larger controls. These enclosures feature padlockable polyester latches, or HOFFMAN's exclusive PowerGlide Handle with 3-point latching, for ease of access with increased security.
Long Description	Hinge Cover Enclosure 3-Point Type 4X, 24.19x24.19x8.00, Gray, Fiberglass
Product Type	FG Wall MT Type 4X 3 PT

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510143565
Manufacturers Part Number	A24H2408GQRLP3PT
UPC	783510143565

Taxonomies, Classifications, and Categories

Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures
------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	32

Uses, Certifications, and Standards

Application	Corrosive Environments; Controls and Drives
nema rating	4X Watertight, corrosion-resistant