



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A30H2408SSLP 30X24X8" N4X SS4 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A30H2408SSLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 30X24X8, Brushed, SS304
Weight per unit	59.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel 304

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Depth	8
Height	30
Size	30.00x24.00x8.00 in
Width	24

Descriptions

Description	30X24X8" N4X SS4 CH CLMP CVR
extra long description	NVENT HOF A30H2408SSLP Stainless En
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 30x24x8, Brushed, SS304
Product Type	Stainless Encl. 30.00X24.00X8.

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510241100
Manufacturers Part Number	A30H2408SSLP
UPC	783510241100

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	59

Uses, Certifications, and Standards

Application	Corrosive Environments; Controls and Drives
nema rating	4X Watertight, corrosion-resistant