



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A363614CTCJ 36X36X14 N3R SC Trans CBT

*Hoffman Enclosures, Inc.*

|                  |  |
|------------------|--|
| Catalog Number   | A363614CTCJ  |
| Manufacturer     | Hoffman Enclosures, Inc.   |
| Description      | Cabinet, Steel, Screw Cover, Flush Mount, Gray, Galvanized Paint, 36 In Overall Width, 36 In Overall Length, 14 In Overall Height, 5 Knockouts, 165.0 LB |
| Weight per unit  | 165.0 (lbs/each)   |
| Product Category | Nema Types 3 & 3R Metallic Enc   |

### Material, Color, and Finish

|            |            |
|------------|------------|
| Color Code | ANSI 61    |
| Finish     | Galvanized |

### Dimensions and Weight

|       |                      |
|-------|----------------------|
| Depth | 14                   |
| Size  | 36.00x36.00x14.00 in |
| Width | 36                   |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 36X36X14 N3R SC TRANS CBT   |
| extra long description | NVENT HOF A363614CTCJ Screw Cover C   |
| Features               | CT Cabinet, Screw-Cover with Steel Foot-Mount Panel, Type 3R offers the flexibility of mounting instrument current transformer vertically or horizontally, and are available in a variety of sizes, models to fit a wide range of outdoor applications. |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Nvent Hoffman  |
| GTIN  | 00783510145170 |
| UPC   | 783510145170   |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | STEEL JUNCTION BOXES                      |
| Type                 | Utility / Canadian Cabinets and Splitters |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 165 |

### Uses, Certifications, and Standards

|             |                                   |
|-------------|-----------------------------------|
| nema rating | 3R Weather-resistant, except dust |
|-------------|-----------------------------------|