



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A530M 30 Min Twist Timer Ivory

Nsi Industries

Catalog Number	A530M
Manufacturer	Nsi Industries
Description	Timer, 30 Min Time Setting Mode, SPDT Contact Form, 30 Min Time Setting, 125/250/277 V Ac, 1 Pole, Ivory, +32 °F Operating Temperature, +122 °F Operating Temperature, 3 X 5 In Size, 0.4 LB
Weight per unit	0.4000 (lbs/each)
Product Category	Electromechanical Time Switches

Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	30 Minute

Descriptions

Description	30 MIN TWIST TIMER IVORY
extra long description	TORK A530M Interval Timer 30 Min Lt

Manufacturer Information

GTIN	00786261150141
UPC	786261150141

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Spring Wound In Wall Time Switch

Packaging

Carton	1
Package	6
Weight Per each	0.4

Uses, Certifications, and Standards

Enclosure	Single Gang Wall Plate
environmental conditions	32-122 F
Frequency Rating	50-60 Hz
Mounting	Single Gang Wall Plate
Operating Temperature	32-122 F
standard	cULus