



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A560M 60 Min Twist Timer Ivory

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | A560M  |
| Manufacturer     | Nsi Industries   |
| Description      | Timer, 60 Min Time Setting Mode, SPDT Contact Form, 60 Min Time Setting, 125/250/277 V Ac, 1 Pole, Ivory, +32 °F Operating Temperature, +122 °F Operating Temperature, 3 X 5 In Size, 0.4 LB |
| Weight per unit  | 0.4000 (lbs/each)  |
| Product Category | Electromechanical Time Switches  |

### Features

|                |                 |
|----------------|-----------------|
| action         | SPDT            |
| Base           | Wall Plate      |
| Contact Rating | 125-250-277 VAC |
| Phase          | Single Phase    |
| Poles          | 1               |
| Timing Range   | 60 Minute       |

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | 60 MIN TWIST TIMER IVORY            |
| extra long description | TORK A560M Interval Timer 60 Min Ho |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00786261150158 |
| UPC  | 786261150158   |

### Taxonomies, Classifications, and Categories

|                      |                                  |
|----------------------|----------------------------------|
| Category Description | TIME CLOCKS                      |
| Type                 | Spring Wound In Wall Time Switch |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 0.4 |

### Uses, Certifications, and Standards

|                          |                        |
|--------------------------|------------------------|
| Enclosure                | Single Gang Wall Plate |
| environmental conditions | 32-122 F               |
| Frequency Rating         | 50-60 Hz               |
| Mounting                 | Single Gang Wall Plate |
| Operating Temperature    | 32-122 F               |
| standard                 | cULus                  |