



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A88116RT 8X8X116 N3R SC Wway

Hoffman Enclosures, Inc.

| | |
|------------------|---|
| Catalog Number | A88116RT |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Wiring Trough Nema Type 3R, 8.00X8.00X116.00, Gray, Steel |
| Weight per unit | 94.6 (lbs/each) |
| Product Category | Nema Type 3R Trough & Gutter |

Features

| | |
|-----------|------------|
| ip rating | IP32 |
| Material | MILD STEEL |

Material, Color, and Finish

| | |
|------------|------------|
| Color | Gray |
| Color Code | ANSI 61 |
| Finish | Galvanized |

Dimensions and Weight

| | |
|-------|---------------------|
| Depth | 116 |
| Size | 8.00x8.00x116.00 in |
| Width | 8 |

Descriptions

| | |
|------------------------|--|
| Description | 8X8X116 N3R SC WWAY |
| extra long description | NVENT HOF A88116RT 8x8x116 3R Wire |
| Features | Screw-Cover Wiring Trough, Type 3R is used for protecting wire and cable distribution, junctions and terminations in outdoor applications that may be exposed to wet conditions. A Padlock Hasp Kit can be installed for increased security. |
| Long Description | Wiring Trough NEMA Type 3R, 8.00x8.00x116.00, Gray, Steel |
| Product Type | 8X8X116 3R Wire Trough |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510133412 |
| Manufacturers Part Number | A88116RT |
| UPC | 783510133412 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type | Trough |

Packaging

| | |
|-----------------|---------|
| Carton | 1 |
| Weight Per each | 94.5999 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | Power Distribution |
| nema rating | 3R Weather-resistant, except dust |