

# Eaton AAL06-C2-K

Catalog Number: AAL06-C2-K

Eaton Smart Dimmer, Light almond, White, 60 Hz, Polycarbonate, Flush, Single-pole, Single-pole, multi-location, 120 Vac, 300W, Wire leads



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton smart dimmer	AAL06-C2-K
<b>UPC</b>	<b>Product Length/Depth</b>
032664730856	2.8 in
<b>Product Height</b>	<b>Product Width</b>
6.13 in	4.4 in
<b>Product Weight</b>	<b>Certifications</b>
0.6 lb	cULus Listed NOM

## Product specifications

### Switch type

Single-pole, multi-location  
Dimmer switch

### Phase

Single-phase

### Termination style

Back and side wire

### Load type

ELV  
CFL  
Dimmable LED  
INC  
MLV  
HAL

### Operating temperature - min

-4 °F

### Color

White  
Light almond

### Wiring method

Wire leads

### Grade

Residential

### Material

Polycarbonate

### Mounting method

Flush

### Number Of Poles

Single-pole

### Number of gangs

2  
3  
1

### Type

Dimmer

### Power consumption

300 W  
300 - 600 W

## Resources

### Installation videos

[How to install Eaton's universal slide dimmers](#)

### Specifications and datasheets

[Eaton Specification Sheet - AAL06-C2-K](#)

Style type

Decorator

Environmental conditions

Dry

Operating temperature - max

158 °F

Frequency rating

60 Hz

Number of ways

Three-way

Voltage rating

120 V

Torque rating

14 lbf-inch



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)