
TOSLINK AUDIO CABLE W/ MINI-ADAPTERS (12 FT)

AC2412-BK | [On-Q](#)



FEATURES & BENEFITS

Toslink optical digital cables use light to transfer the audio signal; eliminating any chance for RFI, EMI or ground loop interference. Connect the Toslink cable using one of the mini Toslink Adapters to any audio device such as DVD player, CD player, satellite receiver, game console or other digital audio equipment for clear, fully detailed sound. Manufactured from high quality PMMA (Poly methyl methacrylate) optical fiber with a polished lens and gold-plated collet, the Toslink cable provides an accurate digital signal. The in-wall rated cable jacket allows for code compliant wall-mount flat panel installs. Available in 3 feet, 6 feet, 12 feet and 25 feet.

- In-Wall Rated for professional installations
- Cables ship with two mini Toslink adapters for ultimate flexibility
- Low loss PMMA (Poly methyl methacrylate) core ensures low distortion
- Includes end caps to protect the conductor from dust, dirt and other material

SPECIFICATIONS

GENERAL INFO

Color: Black

Connection Type: Mini Toslink

Special Features: Supports highest quality digital audio over fiber

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 26121607

DIMENSIONS

Depth (US): 0.70 in.

Height (US): 9.64 in.

Length (US): 12 ft.

Width (US): 7.87 in.

Weight: 0.285 lbs.

Height: 9.64 in.