
STEREO 3.5MM M/M AUDIO CABLE (12 FT)

AC2612-BK | [On-Q](#)



FEATURES & BENEFITS

Designed to provide quality music transfer from your mobile device to a fixed audio device. The unique "Case-Connect" design accommodates secure connections without requiring the removal of your device's protective case. This cable features two 27 AWG oxygen-free copper conductors, a drain wire, an aluminum foil shield to prevent unwanted EMI/RFI interference, and fully molded, gold-plated connectors providing strain relief for a quality connection. Available in 12 feet and 25 feet.

- In-wall, CMG/CL3/FT4 Tri-Rated jacket
- 22 AWG conductor construction
- Case Connect design accommodates secure connections without removing the device's protective case
- Supports a stereo audio signal

SPECIFICATIONS

GENERAL INFO

Color: Black

Connection Type: 3.5mm Audio

Special Features: In-wall, CMG/CL3/FT4 tri-rated jacket, 28 AWG conductor construction, Case Connect, Supports a stereo audio signal

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UN SPSC: 26121616

DIMENSIONS

Depth (US): 0.82 in.

Height (US): 7.5 in.

Length (US): 12 ft.

Width (US): 4.75 in.

Weight: 0.11 lbs.

Height: 7.5 in.

TECHNICAL INFORMATION

Operating Temperature (Celsius): 75° C