

Eaton ACD222URNM

Catalog Number: ACD222URNM

Eaton air conditioning disconnect, Non-fused pullout, 60A, 120/240V, 10 kAIC, #14-2 Cu/Al 60°C or 75°C, NEMA 3R Polycarbonate enclosure, 3 hp at 120V, 10 hp at 240V, Black



General specifications

Product Name

Eaton air conditioning disconnect

Catalog Number

ACD222URNM

UPC

786676406086

Product Length/Depth

5 in

Product Height

8.63 in

Product Width

3.5 in

Product Weight

15 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

CSA Certified

Catalog Notes

For replacement pullout head, order part number 96-3258-4.

Type

Air conditioning disconnect

Amperage Rating

60A

Horsepower

3 hp at 120 V, 10 hp at 240 V

Voltage rating

120/240 V

Wire size

#14-2 AWG Cu/Al

Color

Black

Enclosure

NEMA 3R

Enclosure material

Polycarbonate

Interrupt rating

10 kAIC

Brochures

[Air Conditioning Disconnects](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - ACD222URNM](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia