



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AE80BL 80CFM Fan W/Led Light 1.5 Sones

Broan/Nutone LLC

Catalog Number	AE80BL
Manufacturer	Broan/Nutone LLC
Description	Bath Fan and Light, Ceiling Type; 9-1/4 Inch Length X 10 Inch Width X 5-3/4 Inch Height Size; UL, Hvi Approval; 120 Volt Voltage Rating; 0.5 Amp Current Rating; Yes Lamp Included; Led Lamp Type; 11 Watt Lamp Wattage
Weight per unit	9.2 (lbs/each)
Product Category	Exhaust Fans

### Features

Air Flow Rate	80 CFM
Current Rating	0.5 Amp
Duct Shape	Round
Duct Size	4 Inch Diameter
Grill Finish	White
Grill Shape	Rectangular
Grill Size	11-3/4 Inch Length x 12-1/2 Inch Width
Housing Shape	Rectangular
Lamp Included	Yes
Lamp Type	LED
Lamp Wattage	11 Watt
Sound Level	1.5 SONES
Ventilation Area	75 Square Foot (Bathroom)
Voltage Rating	120 Volt

### Material, Color, and Finish

Grill Material	Polymeric
Housing Material	26 Gauge Rugged Galvanized Steel

### Dimensions and Weight

Size	9-1/4 Inch Length x 10 Inch Width x 5-3/4 Inch Height
------	---



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Additional Information	Power Rating 26.9 Watt; Includes Grille, Blower, Dimming Control
Commodity Description	Exhaust Fans
Description	80CFM FAN W/LED LIGHT 1.5 SONES
extra long description	CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT VOLTAGE RATING; 0.5 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE; 26 GAUGE RUGGED GALVANIZED STEEL HOUSING MATERIAL; 80 CFM AIR FLOW RATE; 4 INCH DIAMETER DUCT SIZE; 1.5 SONES SOUND LEVEL; 11-3/4 INCH LENGTH X 12-1/2 INCH WIDTH GRILL SIZE; POLYMERIC GRILL MATERIAL; RECTANGULAR HOUSING SHAPE; ROUND DUCT SHAPE; RECTANGULAR GRILL SHAPE; WHITE GRILL FINISH; 75 SQUARE FOOT (BATHROOM
Long Description	BATH FAN AND LIGHT, CEILING TYPE; 9-1/4 INCH LENGTH X 10 INCH WIDTH X 5-3/4 INCH HEIGHT SIZE; UL, HVI APPROVAL; 120 VOLT VOLTAGE RATING; 0.5 AMP CURRENT RATING; YES LAMP INCLUDED; LED LAMP TYPE; 11 WATT LAMP WATTAGE
Product Type	Bath Fan and Light

## Manufacturer Information

Brand	BROAN
GTIN	00026715239573
Manufacturers Part Number	AE80BL
UPC	026715239573

## Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	CEILING

## Packaging

Carton	1
Weight Per each	9.16

## Uses, Certifications, and Standards

Approval	UL, HVI
----------	---------