



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AGC110 1/10A 250V 1/4X1-1/4 Rohs Fa Glass Fuse

Bussmann Fuses

Catalog Number	AGC110
Manufacturer	Bussmann Fuses
Description	1/10A 250V 3AG - 1/4" X 1-1/4" Glass, Fast Acting Fuse
Weight per unit	0.0100 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	1/10 Amp
connection	Ferrule End X Ferrule End
Response Time	60 Min Maximum at 135%, 120 S Maximum at 200%
type of indicators	Non-Indicating
Voltage Rating	250 VAC

Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

Descriptions

Description	1/10A 250V 1/4X1-1/4 ROHS FA GLASS FUSE
extra long description	EFSE AGC-1/10 \BUSS SMALL DIMENSION
Long Description	1/10A 250V 3AG - 1/4" x 1-1/4" Glass, Fast Acting Fuse
Product Type	\Buss Small Dimension Fuse Fast Acting
Special Features	Interrupt Rating 35 Amp at 250 Vac, 10000 Amp at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap

Manufacturer Information

Brand	Cooper Bussmann North America
GTIN	00051712703642
Manufacturers Part Number	AGC-1/10
UPC	051712703642

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Electronic, Fast Acting

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	5
Weight Per each	0.01



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application
standard

Electronic Circuits
UL 248-14, CSA