



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AGC12 12A 250V 1/4X1-1/4 Non-Rohs Fa Glass Fuse *Bussmann Fuses*

Catalog Number	AGC12
Manufacturer	Bussmann Fuses
Description	2/10A 125V 3AG - 1/4" X 1-1/4" Glass, Fast Acting Fuse
Weight per unit	0.0060 (lbs/each)
Product Category	Tools & Testers

### Features

amperage rating	12 Amp
connection	Ferrule End X Ferrule End
Response Time	60 Min Maximum at 135%, 120 S Maximum at 200%
type of indicators	Non-Indicating
Voltage Rating	250 VAC

### Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

### Descriptions

Description	12A 250V 1/4X1-1/4 NON-ROHS FA GLASS FUSE
extra long description	EFSE AGC-12 BUSS SMALL DIMENSION FU
Long Description	2/10A 125V 3AG - 1/4" x 1-1/4" Glass, Fast Acting Fuse
Product Type	Buss Small Dimension Fuse 5N Auto Pack
Special Features	Interrupt Rating 35 Amp at 250 Vac, 1000 Amp at 32 Vac, Material Glass Tube, Nickel Plated Brass Endcap

### Manufacturer Information

Brand	Cooper Bussmann North America
GTIN	00051712703789
Manufacturers Part Number	AGC-12
UPC	051712703789

### Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Electronic, Fast Acting

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	5
Weight Per each	0.006

### Uses, Certifications, and Standards

Application	Electronic Circuits
standard	UL 248-14, CSA, CE