

# Specifications



Photo is representative



## Eaton AGC-2-1/2-R

Eaton AGC series Fast-acting fuse 2.5A, 250 Vac, 32 Vdc (self certified), AGC-2-1-2-R

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series AGC fast-acting glass tube fuse
<b>CATALOG NUMBER</b>	AGC-2-1/2-R
<b>UPC</b>	051712655064
<b>PRODUCT LENGTH/DEPTH</b>	1.25 in
<b>PRODUCT HEIGHT</b>	0.25 in
<b>PRODUCT WIDTH</b>	0.25 in
<b>PRODUCT WEIGHT</b>	0.01 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	CE Marked RoHS Compliant



Powering Business Worldwide

## Product specifications

USED WITH	out axial leads
AMPERAGE RATING	2.5 A
INTERRUPT RATING	100 AIC at 250 Vac 10 kAIC at 125 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	60 min at 135%, 120 sec at 200%
MATERIAL	Glass tube Nickel-plated brass end cap construction
QUANTITY	5
VOLTAGE RATING	250 Vac, 32 Vdc (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - AGC-2-1/2-R](#)

[Eaton AGC fast-acting glass tube fuses data-sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton AGC-2-1/2-R

Eaton AGC series Fast-acting fuse 2.5A, 250 Vac, 32 Vdc (self certified), AGC-2-1-2-R

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series AGC fast-acting glass tube fuse
<b>CATALOG NUMBER</b>	AGC-2-1/2-R
<b>UPC</b>	051712655064
<b>PRODUCT LENGTH/DEPTH</b>	1.25 in
<b>PRODUCT HEIGHT</b>	0.25 in
<b>PRODUCT WIDTH</b>	0.25 in
<b>PRODUCT WEIGHT</b>	0.01 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	CE Marked RoHS Compliant



Powering Business Worldwide

## Product specifications

USED WITH	out axial leads
AMPERAGE RATING	2.5 A
INTERRUPT RATING	100 AIC at 250 Vac 10 kAIC at 125 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	60 min at 135%, 120 sec at 200%
MATERIAL	Glass tube Nickel-plated brass end cap construction
QUANTITY	5
VOLTAGE RATING	250 Vac, 32 Vdc (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - AGC-2-1/2-R](#)

[Eaton AGC fast-acting glass tube fuses data-sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

