

Specifications



Photo is representative



Eaton AGC-2-1/2-R

Eaton AGC series Fast-acting fuse 2.5A, 250 Vac, 32 Vdc (self certified), AGC-2-1-2-R

General specifications

PRODUCT NAME	Eaton Bussmann series AGC fast-acting glass tube fuse
CATALOG NUMBER	AGC-2-1/2-R
UPC	051712655064
PRODUCT LENGTH/DEPTH	1.25 in
PRODUCT HEIGHT	0.25 in
PRODUCT WIDTH	0.25 in
PRODUCT WEIGHT	0.01 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant



Powering Business Worldwide

Product specifications

USED WITH	out axial leads
AMPERAGE RATING	2.5 A
INTERRUPT RATING	100 AIC at 250 Vac 10 kAIC at 125 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	60 min at 135%, 120 sec at 200%
MATERIAL	Glass tube Nickel-plated brass end cap construction
QUANTITY	5
VOLTAGE RATING	250 Vac, 32 Vdc (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - AGC-2-1/2-R](#)

[Eaton AGC fast-acting glass tube fuses data-sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

