

Eaton AH1191N

Catalog Number: AH1191N

Eaton locking switch, Corbin type, #14-10 AWG, 20A, 120/277V, Back and side wiring, Key actuator, Maintained closure, Brown, Single-pole, Urea



General specifications

Product Name	Catalog Number
Eaton locking switch	AH1191N
UPC	Product Length/Depth
040893627793	1.31 in
Product Height	Product Width
3.28 in	1.34 in
Product Weight	Warranty
0.45 lb	Refer to warranty document.
Compliances	Certifications
NAFTA RoHS Compliant	cULus Listed

Product specifications

Special features

Corbin type locking

Switch type

Single-pole

Closure type

Maintained

Color

Brown

Wiring method

Back and side

Material

Urea

Allowable wire size

#14-10 AWG

Amperage Rating

20A

Type

Switch

Voltage rating

120/277 V

Torque rating

14 lbf-inch

Application

Industrial

Actuator

Key

Resources

Catalogs

[Arrow Hart Buyers Guide Section E](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - AH1191N](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)