

Specifications



Photo is representative



Eaton AH1221W

Eaton Arrow Hart industrial grade toggle switch, #14-10 AWG, 20A, Industrial, Flush, 120/277V, Back and side, Screw, White, Single-Pole, Single-Pole, Brass, Polycarbonate

General specifications

PRODUCT NAME	Eaton Arrow Hart industrial grade toggle switch
CATALOG NUMBER	AH1221W
UPC	032664734694
PRODUCT LENGTH/DEPTH	1.3 in
PRODUCT HEIGHT	4.19 in
PRODUCT WIDTH	1.005 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	cULus Listed NOM Federal Specification Classification W-S-896E
PRODUCT TYPE	Industrial grade toggle switch

Product specifications

TYPE	Toggle switch
AMPERAGE RATING	20A
VOLTAGE RATING	120/277 V
NUMBER OF POLES	Single-pole
APPLICATION	Industrial
WIRING METHOD	Back and side
SWITCH TYPE	Single-pole
MOUNTING METHOD	Flush
CONNECTOR TYPE	Screw
MATERIAL	Polycarbonate
ALLOWABLE WIRE SIZE	#14-10 AWG
TORQUE RATING	14 lbf-inch
TERMINAL ENCLOSURE MATERIAL	Brass
TERMINALS	0.031 in
COLOR	White

Resources

MULTIMEDIA

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - AH1221W](#)

[Arrow Hart extra heavy-duty industrial grade AC toggle switches spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

