



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AH1224W SW TOGGLE4WAY 20A 120/277VAUTOGRD B&S WH

*Eaton Wiring Devices*

Catalog Number	AH1224W
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Industrial Grade Toggle Switch, #14-10 Awg, 20A, Industrial, Wall, 120/277V, Back and Side, Screw, White, Four-Way, Brass, Terminals: 0.031 In, Polycarbonate
Weight per unit	0.0100 (lbs/each)
Product Category	Disconnect Motor Switches

### Features

amperage rating	20
dimensions	1.0300 IN X 1.3000 IN X 2.4000 IN
Material	Polycarbonate
media	Yes
Poles	1
Voltage Rating	120/277 V

### Descriptions

Description	SW TOGGLE4WAY 20A 120/277VAUTOGRD B&S WH
extra long description	EWD AH1224W SW Toggle4Way 20A 120/2
Features	Eaton's Arrow Hart broad line of extra heavy-duty industrial grade switches feature superior engineering, reliable performance and ease of installation. Available in toggle, lighted, pilot light, Corbin and locking versions.
Long Description	Eaton Arrow Hart industrial grade toggle switch, #14-10 AWG, 20A, Industrial, Wall, 120/277V, Back and side, Screw, White, Four-way, Brass, Terminals: 0.031 in, Polycarbonate
Product Type	SW TOGGLE4WAY 20A 120/277VAUTOGRD B&S WH
Special Features	Commercial Grade

### Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00032664734946
Manufacturers Part Number	AH1224W
UPC	032664734946

### Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Industrial grade toggle switch

### Packaging

Carton	1
Package	10
Weight Per each	0.01



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility - Other
standard	NOM,cULus Listed,Federal Specification Classification W-S-896E