



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AH330R6W Recp Pin&Sleeve 30A 250V 2P3W WT BL *Eaton Wiring Devices*

Catalog Number	AH330R6W
Manufacturer	Eaton Wiring Devices
Description	Eaton Arrow Hart Pin and Sleeve Receptacle, IP69K Rated, #10 -#2 Awg, 30A, Extra Heavy-Duty, 250V, Back Wire, Blue, Nickel Plated Brass, IP67, IP69K, Nylon, Two-Pole, Three-Wire, Grounding, AHBB30 Back Box Style, Female, Nylon
Weight per unit	32.0 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	30
connection	Pin & Sleeve
dimensions	3.7500 IN X 4.2100 IN X 3.1250 IN
insulation	Nylon PA6-GF30FR (17)
Material	Nylon
media	Yes
Phase	1
Poles	2
Voltage Rating	250V/AC

Material, Color, and Finish

Color	Blue & Gray
-------	-------------

Dimensions and Weight

Size	5.5 x 4.75 x 5
------	----------------

Descriptions

Description	RECP PIN&SLEEVE 30A 250V 2P3W WT BL
extra long description	EWD AH330R6W Recp Pin&Sleeve 30A 25
Features	Eaton's Arrow Hart full line of pin and sleeve devices offer sturdy nylon construction, rugged design with corrosion resistant components for lasting electrical performance, and watertight sealing that provides IP69K protection so you can feel confident in even the most severe washdown environments.
Long Description	Eaton Arrow Hart pin and sleeve receptacle, IP69K Rated, #10 -#2 AWG, 30A, Extra Heavy-Duty, 250V, Back wire, Blue, Nickel plated brass, IP67, IP69K, Nylon, Two-pole, Three-wire, grounding, AHBB30 Back box style, Female, Nylon
Product Type	Recp Pin&Sleeve 30A 250V 2P3W WT BL
Special Features	Watertight P&S receptacles



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00032664731938
Manufacturers Part Number	AH330R6W
UPC	032664731938

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	RECEPTACLE

Packaging

Carton	1
Package	32
Weight Per each	32

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
environmental conditions	IP67 & IP69k
Mounting	Flange Mount
standard	IEC, UL, CSA
Temperature Rating	Max. 30°C (86°F) after 50 cycles of overload @150% of rated current