



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AH430R7W Recept Pin&Sleeve 30A 480V 3PH 3P4W WT RD *Eaton Wiring Devices*

Catalog Number	AH430R7W
Manufacturer	Eaton Wiring Devices
Description	Receptacle Pin and Sleeve 30 Amp 480 Volt 3 Phase 3 Pole 4 Wire WT Red
Weight per unit	2.0 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	30
connection	Pin & Sleeve
dimensions	3.7500 IN X 4.2100 IN X 3.1250 IN
insulation	Nylon PA6-GF30FR (17)
Material	Nylon;Other
media	Yes
Phase	3
Poles	3
Voltage Rating	3Ø 480V/AC

### Material, Color, and Finish

Color	Blue & Gray
-------	-------------

### Dimensions and Weight

Size	5.5 x 4.75 x 5
------	----------------

### Descriptions

Description	RECP PIN&SLEEVE 30A 480V 3PH 3P4W WT RD
extra long description	CRS-H AH430R7W RECP PIN AND SLEEVE
Features	Eaton's Arrow Hart full line of pin and sleeve devices offer sturdy nylon construction, rugged design with corrosion resistant components for lasting electrical performance, and watertight sealing that provides IP69K protection so you can feel confident in even the most severe washdown environments.
Long Description	RECEPTACLE PIN AND SLEEVE 30 AMP 480 VOLT 3 PHASE 3 POLE 4 WIRE WT RED
Product Type	Recept Pin and Sleeve 30A 480V 3PH 3P4W WT
Special Features	Watertight P&S receptacles

### Manufacturer Information

Brand	Eaton
GTIN	00326647319764
Manufacturers Part Number	AH430R7W
UPC	032664731976



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	RECEPTACLE

## Packaging

Carton	1
Package	32
Weight Per each	2

## Uses, Certifications, and Standards

Application	IEC 309 Products
environmental conditions	IP67 & IP69k
Mounting	Flange Mount
standard	IEC, UL, CSA
Temperature Rating	Max. 30°C (86°F) after 50 cycles of overload @150% of rated current