



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AH460R12W Recept Pin&Sleeve 60A 125/250V 3P4W WT or *Eaton Wiring Devices*

Catalog Number	AH460R12W
Manufacturer	Eaton Wiring Devices
Description	CRS-H AH460R12W Recept Pin and Sleeve
Weight per unit	32.0 (lbs/each)
Product Category	Pin & Sleeve Devices

### Features

amperage rating	60
connection	Pin & Sleeve
dimensions	6.5000 IN X 5.0000 IN X 5.1250 IN
insulation	Nylon PA6-GF30FR (17)
Material	Nylon
media	Yes
Phase	3
Poles	3
Voltage Rating	125/250V/AC

### Material, Color, and Finish

Color	Blue & Gray
-------	-------------

### Dimensions and Weight

Size	6.5 x 5 x 5.125
------	-----------------

### Descriptions

Description	RECP PIN&SLEEVE 60A 125/250V 3P4W WT OR
Features	Eaton's Arrow Hart full line of pin and sleeve devices offer sturdy nylon construction, rugged design with corrosion resistant components for lasting electrical performance, and watertight sealing that provides IP69K protection so you can feel confident in even the most severe washdown environments.
Long Description	CRS-H AH460R12W RECP PIN AND SLEEVE
Product Type	Recept Pin and Sleeve 60A 125/250V 3P4W WT
Special Features	Watertight P&S receptacles

### Manufacturer Information

Brand	Eaton
GTIN	00040893619897
Manufacturers Part Number	AH460R12W
UPC	040893619897



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	RECEPTACLE

## Availability

Manufacturer Status	Inactive
---------------------	----------

## Packaging

Carton	1
Package	16
Weight Per each	32

## Uses, Certifications, and Standards

Application	IEC 309 Products
environmental conditions	IP67 & IP69k
Mounting	Flange Mount
standard	IEC, UL, CSA
Temperature Rating	Max. 30°C (86°F) after 50 cycles of overload @150% of rated current