



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AH6808UDAC Man Cont 20/30A 600/250VAC 2POLE B&S BK

Eaton Wiring Devices

Catalog Number	AH6808UDAC
Manufacturer	Eaton Wiring Devices
Description	Eaton Manual Motor Controller, #14-10 Awg, 20/30A, Industrial, Wall, 600/250V, Back and Side, Maintained Contact, Black, Open, Two-Pole, -20-65 C, Single-Phase, Toggle Switch, Copper-Alloy Terminal, Brass Screw, Single-Throw, Thermoset
Weight per unit	N/A
Product Category	Disconnect Motor Switches

Descriptions

Description	MAN CONT 20/30A 600/250VAC 2POLE B&S BK
extra long description	EWD AH6808UDAC Man Cont 20/30A 600/
Features	Eaton's Arrow Hart manual motor controllers offer compact, industrial-grade designs built to provide safe, reliable motor control performance in even the most rugged environments. They feature high-impact-resistant, glass-filled nylon construction; easy-to-read electrical ratings on rugged steel mounting straps; clear ON/OFF indicators on large, rugged toggles; distinct wire pockets and thick-wall arc barriers to contain strands; and screw-and-clamp or box-lug terminals to meet individual project requireme
Long Description	Eaton manual motor controller, #14-10 AWG, 20/30A,Industrial, Wall, 600/250V, Back and side, Maintained contact, Black, Open, Two-pole, -20-65 C, Single-phase, Toggle switch, Copper-alloy terminal, brass screw, Single-throw, Thermoset
Product Type	Man Cont 20/30A 600/250VAC 2POLE B&S BK
Special Features	Motor control switches, swt/encl combos

Manufacturer Information

Brand	Arrow Hart
GTIN	00040893123905
Manufacturers Part Number	AH6808UDAC
UPC	040893123905

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous commercial & industrial devices
----------------------	-----------------------------------------------

Packaging

Carton	1
Package	50
Weight Per each	0