



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

903 Mississippi Ave  
76301-0000, TX Wichita Falls  
Phone: 940-257-6832  
Fax: 940-257-6833



## AH6810W AH6810U In Nema 3R Enclosure

*Eaton Wiring Devices*

Catalog Number	AH6810W
Manufacturer	Eaton Wiring Devices
Description	Eaton Manual Motor Controller, #14-10 Awg, 30A, Wall, 600V, Front Wired, Maintained Contact, Gray, Nema 3R, Enclosure: Copperless Aluminum, Two-Pole, -20-65 C, Single-Phase, Toggle Switch, Copper-Alloy Terminal, Brass Screw, Single-Throw
Weight per unit	3.1 (lbs/each)
Product Category	Definite Purpose Contactors

### Features

amperage rating	30A
dimensions	9.3000 IN X 7.0000 IN X 5.9000 IN
Poles	2
Voltage Rating	600 V

### Descriptions

Description	AH6810U IN NEMA 3R ENCLOSURE
extra long description	EWD AH6810W AH6810U in NEMA 3R Encl
Features	Eaton's Arrow Hart manual motor controllers offer compact, industrial-grade designs built to provide safe, reliable motor control performance in even the most rugged environments. They feature high-impact-resistant, glass-filled nylon construction; easy-to-read electrical ratings on rugged steel mounting straps; clear ON/OFF indicators on large, rugged toggles; distinct wire pockets and thick-wall arc barriers to contain strands; and screw-and-clamp or box-lug terminals to meet individual project requireme
Long Description	Eaton manual motor controller, #14-10 AWG, 30A, Wall, 600V, Front wired, Maintained contact, Gray, NEMA 3R, Enclosure: Copperless aluminum, Two-pole, -20-65 C, Single-phase, Toggle switch, Copper-alloy terminal, brass screw, Single-throw
Product Type	AH6810U In Nema 3R Enclosure
Special Features	With NEMA 3R enclosure

### Manufacturer Information

Brand	Eaton Wiring Devices
GTIN	00040893616865
Manufacturers Part Number	AH6810W
UPC	040893616865



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

903 Mississippi Ave  
76301-0000, TX Wichita Falls  
Phone: 940-257-6832  
Fax: 940-257-6833

## Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Manual motor controller

## Packaging

Carton	1
Weight Per each	3.05

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility - Other
nema rating	3R
Operating Temperature	-20 to 65 °C
standard	cULus Listed,RoHS Compliant,NAFTA