

Eaton's Arrow Hart  
Color coded locking devices

# Eaton's Arrow Hart Color Coded Locking Devices

## Arrow Hart



Eaton's **color coded locking devices** are an **industry-first solution** that adds six voltage rating color codes to locking plugs, connectors, inlets, outlets and receptacles.

**EATON**

*Powering Business Worldwide*

The superior safety of Eaton's Arrow Hart locking devices has been enhanced with **color coding** to provide you a quick, clear and easy way to **identify your circuit voltage**. Designed to provide the long lasting, dependable service you've come to expect from Arrow Hart plugs and connectors, our **color coded locking devices** are the perfect solution for your commercial and industrial applications.

## Features & benefits

- Six color codes consistent with IEC 60309 standard to identify voltage ratings at a glance
- Voltage ratings are printed on device in a location which is visible even when devices are mated
- Ergonomic ultra grip design on plugs and connectors are easier to handle during use
- Double dovetail cord grip provides superior cord alignment and clamp force for wire retention



## Connect with Color

**Find your voltage. Find your NEMA. Find your color.**

Use the chart below to **find the color** for your devices. See our NEMA selector guide for our full product offering.

Voltage	NEMA	Color
125 V/AC	L5	Yellow
125/250 V/AC	L10, L14, Non-NEMA	Orange
250 V/AC	L6	Blue
3Ø 250 V/AC	L11, L15	Blue
3ØY 120/208 V/AC	L18, L21, Non-NEMA	Blue
277 V/AC	L7	Gray
480 V/AC	L8	Red
3Ø 480 V/AC	L16	Red
3ØY 277/480 V/AC	L19, L22	Red
3Ø 600 V/AC	L17	Black
3ØY 347/600 V/AC	L20, L23	Black

**Perfect for:** *Welding, generators, power distribution units, stage and entertainment equipment, trade shows, conventions, temporary power, industrial machinery and equipment*

## Arrow Hart color coded ultra grip locking devices

### 20A Industrial grade locking devices



Plug



Connector

Pole-Wire	NEMA		V/AC	Color	Plug	Connector	Receptacle	Flanged Inlet	Flanged Outlet
2P-3W	L5-20		125	Yellow & black	AHCL520P	AHCL520C	AHCL520R	AHCL520FI	AHCL520FO
	L6-20		250	Blue & black	AHCL620P	AHCL620C	AHCL620R	AHCL620FI	AHCL620FO
	L7-20		277	Gray & black	AHCL720P	AHCL720C	AHCL720R	AHCL720FI	AHCL720FO
	L8-20		480	Red & black	AHCL820P	AHCL820C	AHCL820R	AHCL820FI	AHCL820FO

# Arrow Hart color coded ultra grip locking devices

## 20A Industrial grade locking devices



Plug



Connector



Receptacle



Flanged inlet



Flanged outlet

Pole-Wire	NEMA	V/AC	Color	Plug	Connector	Receptacle	Flanged Inlet	Flanged Outlet
3P-3W	L10-20	125/250	Orange & black	AHCL1020P	AHCL1020C	AHCL1020R	AHCL1020FI	AHCL1020FO
	L11-20	3ØY 250	Blue & black	AHCL1120P	AHCL1120C	AHCL1120R	AHCL1120FI	AHCL1120FO
3P-4W	L14-20	125/250	Orange & black	AHCL1420P	AHCL1420C	AHCL1420R	AHCL1420FI	AHCL1420FO
	L15-20	3ØY 250	Blue & black	AHCL1520P	AHCL1520C	AHCL1520R	AHCL1520FI	AHCL1520FO
	L16-20	3ØY 480	Red & black	AHCL1620P	AHCL1620C	AHCL1620R	AHCL1620FI	AHCL1620FO
4P-4W	L18-20	3ØY 120/208	Blue & black	AHCL1820P	AHCL1820C	AHCL1820R	AHCL1820FI	AHCL1820FO
	L19-20	3ØY 277/480	Red & black	AHCL1920P	AHCL1920C	AHCL1920R	AHCL1920FI	AHCL1920FO
	L20-20	3ØY 347/600	Black & black	AHCL2020P	AHCL2020C	AHCL2020R	AHCL2020FI	AHCL2020FO
4P-5W	L21-20	3ØY 120/208	Blue & black	AHCL2120P	AHCL2120C	AHCL2120R	AHCL2120FI	AHCL2120FO
	L22-20	3ØY 277/480	Red & black	AHCL2220P	AHCL2220C	AHCL2220R	AHCL2220FI	AHCL2220FO
	L23-20	3ØY 347/600	Black & black	AHCL2320P	AHCL2320C	AHCL2320R	AHCL2320FI	AHCL2320FO

## 30A Industrial grade locking devices

Pole-Wire	NEMA	V/AC	Color	Plug	Connector	Receptacle	Flanged Inlet	Flanged Outlet
2P-3W	L5-30	125	Yellow & black	AHCL530P	AHCL530C	AHCL530R	AHCL530FI	AHCL530FO
	L6-30	250	Blue & black	AHCL630P	AHCL630C	AHCL630R	AHCL630FI	AHCL630FO
	L7-30	277	Gray & black	AHCL730P	AHCL730C	AHCL730R	AHCL730FI	AHCL730FO
	L8-30	480	Red & black	AHCL830P	AHCL830C	AHCL830R	AHCL830FI	AHCL830FO

# Arrow Hart color coded ultra grip locking devices

## 30A Industrial grade locking devices

Pole-Wire	NEMA	V/AC	Color	Plug	Connector	Receptacle	Flanged Inlet	Flanged Outlet
3P-3W	L10-30	125/250 L10-30R L10-30P	Orange & black	AHCL1030P	AHCL1030C	AHCL1030R	AHCL1030FI	AHCL1030FO
	L11-30	3ØY 250 L11-30R L11-30P	Blue & black	AHCL1130P	AHCL1130C	AHCL1130R	AHCL1130FI	AHCL1130FO
3P-4W	L14-30	125/250 L14-30R L14-30P	Orange & black	AHCL1430P	AHCL1430C	AHCL1430R	AHCL1430FI	AHCL1430FO
	L15-30	3ØY 250 L15-30R L15-30P	Blue & black	AHCL1530P	AHCL1530C	AHCL1530R	AHCL1530FI	AHCL1530FO
	L16-30	3ØY 480 L16-30R L16-30P	Red & black	AHCL1630P	AHCL1630C	AHCL1630R	AHCL1630FI	AHCL1630FO
	L17-30	3ØY 600 L17-30R L17-30P	Black & black	AHCL1730P	AHCL1730C	AHCL1730R	AHCL1730FI	AHCL1730FO
4P-4W	L18-30	3ØY 120/208 L18-30R L18-320P	Blue & black	AHCL1830P	AHCL1830C	AHCL1830R	AHCL1830FI	AHCL1830FO
	L19-30	3ØY 277/480 L19-30R L19-30P	Red & black	AHCL1930P	AHCL1930C	AHCL1930R	AHCL1930FI	AHCL1930FO
	L20-30	3ØY 347/600 L20-30R L20-30P	Black & black	AHCL2030P	AHCL2030C	AHCL2030R	AHCL2030FI	AHCL2030FO
4P-5W	L21-30	3ØY 120/208 L21-30R L21-30P	Blue & black	AHCL2130P	AHCL2130C	AHCL2130R	AHCL2130FI	AHCL2130FO
	L22-30	3ØY 277/480 L22-30R L22-30P	Red & black	AHCL2230P	AHCL2230C	AHCL2230R	AHCL2230FI	AHCL2230FO
	L23-30	3ØY 347/600 L23-30R L23-30P	Black & black	AHCL2330P	AHCL2330C	AHCL2330R	AHCL2330FI	AHCL2330FO



Plug



Connector



Receptacle



Flanged inlet



Flanged outlet

Electrical Sector  
203 Cooper Circle  
Peachtree City, GA 30269  
United States  
Eaton.com  
Eaton.com/arrowhart

Electrical Sector  
Canada Operations  
5925 McLaughlin Road  
Mississauga, Ontario, L5R 1B8  
Canada  
EatonCanada.ca  
Eaton.com/arrowhart

Electrical Sector  
Mexico Operations  
Carr. Tlalnepantla -  
Cuautitlán Km 178 s/n  
Col. Villa Jardín esq.  
Cerrada 8 de Mayo  
Cuautitlán, Mexico CP 54800  
México  
Eaton.mx  
Eaton.com/arrowhart



Powering Business Worldwide

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

© 2019 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. SA630013EN  
September 2019

Eaton is a registered trademark.  
All other trademarks are property  
of their respective owners.