

Specifications



Eaton AHDS30

Eaton motor control disconnect switch, #14-10 AWG, 30A, Industrial, Mounting feet/DIN rail, flush or 1/4" spacing, 600V, Gray, NEMA 4X, Enclosure: VALOX thermoplastic, Washdown, Three-pole, Three-phase, Rotary switch, Thermoplasti

General specifications

PRODUCT NAME	Eaton motor control disconnect switch
CATALOG NUMBER	AHDS30
UPC	032664741326
PRODUCT LENGTH/DEPTH	8.75 in
PRODUCT HEIGHT	5 in
PRODUCT WIDTH	5.68 in
PRODUCT WEIGHT	3.183 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	cULus Listed
PRODUCT TYPE	Motor control disconnect switch

Product specifications

NEMA RATING	4X
ENCLOSURE	NEMA 4X
TYPE	Motor control disconnect switch
AMPERAGE RATING	30A
VOLTAGE RATING	600 V
NUMBER OF POLES	Three-pole
PHASE	Three-phase
ENCLOSURE MATERIAL	VALOX thermoplastic
APPLICATION	Industrial
DEVICE GRADE	Industrial
ENVIRONMENTAL CONDITIONS	Complex Washdown
SWITCH TYPE	Rotary switch
MOUNTING METHOD	Flush or 1/4 in spacing Mounting feet/DIN rail
ALLOWABLE WIRE SIZE	#14-10 AWG
MATERIAL	Thermoplastic
COLOR	Gray

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - AHDS30](#)

[Non-fused 30 or 60 amp motor control disconnect switch spec sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

