



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AHG22111 Cush Vapor Hang 3/4STEM 3/4 Nip 16-30LB

Crouse-Hinds

Catalog Number	AHG22111
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Ahg Flexible Fixture Hanger, 16-30 LB, 3/4" Luminaire Stem Size, Feraloy Iron Alloy, Pendant Mount, 3/4" Nipple Size, Cushion Type
Weight per unit	2.3 (lbs/each)
Product Category	Lighting Accessories

Features

dimensions	3.2500 IN X 4.0000 IN X 3.8800 IN
Material	Malleable Iron Top Cap, Feraloy Iron Alloy Bottom Cap/Luminaire Stem Support

Dimensions and Weight

Size	3/4 In Fixture Stem, 3/4 In Hub
------	---------------------------------

Descriptions

Description	CUSH VAPOR HANG 3/4STEM 3/4 NIP 16-30LB
extra long description	CRS-H AHG22111 CUSH VAPOR HANG 3/4S
Features	Designed for use with pendant mount industrial or Class I, Division 2 light fixtures, AHG, ARB, UNJ and UNJC flexible fixture hangers from Eaton's Crouse-Hinds Division connect to a conduit hub or the hub cover of a supporting conduit fitting. The ball or cushion type support allows the light fixture to swing in any direction.
Long Description	Eaton Crouse-Hinds series AHG flexible fixture hanger, 16-30 lb, 3/4" luminaire stem size, Feraloy iron alloy, Pendant mount, 3/4" nipple size, Cushion type
Product Type	Cush Vapor Hang 3/4STEM 3/4 Nip 16-30LB

Manufacturer Information

Brand	Crouse-Hinds
GTIN	00782274027401
Manufacturers Part Number	AHG22111
UPC	782274027401

Taxonomies, Classifications, and Categories

Type	Flexible Fixture Hanger
------	-------------------------

Packaging

Carton	2
Weight Per each	2.25



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application Ind Facilities & Factories - Facility: Lighting and Lighting Controls