

Eaton AN19BN0A5E020

Catalog Number: AN19BN0A5E020

Eaton Freedom NEMA Starter, Full voltage non-reversing, C440 electronic overload relay, NEMA Size 0 open enclosure - 18 A, Horizontal mounting, 120/60 or 110/50 coil voltage, C440 standard feature set - 4–20 A



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control starter	AN19BN0A5E020
	UPC
	786685414706
Product Length/Depth	Product Height
4.9 in	6.6 in
Product Width	Product Weight
1.97 in	1.75 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL	
CSA	
CE	
NEMA	

defaultTaxonomyAttributeLabel

NEMA frame size

NEMA Size 0

Relay

C440 electronic

Type

Starter

Special features

With C440 EOLR standard feature set, SEL reset, SEL class (10a, 10, 20, 30)

Configuration

Non-reversing

Amperage Rating

18 A

Size

0

Mounting

Horizontal

Overload relay

C440 electronic

Coil voltage

120/60 or 110/50

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[AN19BN0_5 AutoCAD 2D Footprint](#)

[AN19BN0_5 3D Model Xchange](#)

[AN19BN0_5 3D Inventor](#)

[AN19BN0_5 2D PDF](#)

[AN19BN0_5 2D Drawing Xchange](#)

[AN19BN0_5 AutoCAD 2D Footprint \(mm\)](#)

Specifications and datasheets

[Eaton Specification Sheet - AN19BN0A5E020](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)