



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1701 North Jackson Suite E
78501-0000, TX McAllen
Phone: 956-331-2410
Fax: 956-331-2411



B12N 12-10 Nylon Butt Splice

Nsi Industries

Catalog Number	B12N
Manufacturer	Nsi Industries
Description	Seamless Butt Splice Constructed From Electro Tin-Plated Copper Tubing With Nylon Insulation. Features A Center Stop to Insure Equal Insertion Of Wires. Used For Wire Splicing In 12-10 Awg Applications
Weight per unit	0.2500 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Material	Copper, Nylon
Number of Terminals	2
Terminal Size	1.063 Long
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	12-10 AWG

Material, Color, and Finish

Color	Yellow
Finish	Tin Plated

Descriptions

Description	12-10 NYLON BUTT SPLICE
extra long description	NSI B12-N 12-10 Awg Nylon Insulated
Features	12-10 AWG Nylon Insulated Butt Splice, 50/Pack
Long Description	Seamless Butt Splice constructed from electro tin-plated copper tubing with nylon insulation. Features a center stop to insure equal insertion of wires. Used for wire splicing in 12-10 AWG applications
Product Type	12-10 Awg Nylon Insulated Butt Splice, 50/Pack
Special Features	Nylon Insulated 12-10 AWG - 50 Pack

Manufacturer Information

Brand	NSi
GTIN	00662381069863
Manufacturers Part Number	B12-N
UPC	662381069863

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Nylon Insulated Butt Connectors



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1701 North Jackson Suite E
78501-0000, TX McAllen
Phone: 956-331-2410
Fax: 956-331-2411

Availability

minimum qty 50

Packaging

Carton 1

Package 50

Weight Per each 0.25

Uses, Certifications, and Standards

Application Wire Splicing

environmental conditions 105 C

standard cULus