



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **B2350JR B-Cap Wire Connector, Model B2 Red, 350/Jar**

*Ideal*

|                  |  |
|------------------|--|
| Catalog Number   | B2350JR  |
| Manufacturer     | Ideal  |
| Description      | Buchanan, Wire Connector, B-Cap, Conductor Range: 22 - 8 Awg, 2/18 Awg Min, 5/12 Awg Max, Number Of Conductors: 2 to 6, Material: Flame-Retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: B2 |
| Weight per unit  | N/A  |
| Product Category | Large Terminals & Connectors   |

### **Features**

|                |                               |
|----------------|-------------------------------|
| Material       | Flame-retardant Polypropelene |
| Voltage Rating | 600                           |

### **Material, Color, and Finish**

|       |     |
|-------|-----|
| Color | Red |
|-------|-----|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | B-CAP WIRE CONNECTOR, MODEL B2 RED, 350/JAR   |
| extra long description | IDEAL B2-350JR B-CAP B2 RED, 350 JA   |
| Features               | The B-CAP Wire Connector gets you in those hard-to reach spots comfortably, especially when you're retrofitting or updating. Slim, classic fins and an expanding interior spring give the B-CAP a secure grip with extra leverage, making it the most compact connector on the market for up to 5 #12 (Red Model B2).The unique, space-saving profile of the B-CAP makes it perfect for retrofit work and shallow boxes.The B-CAP also features a tough, flame-retardant shell that withstands environmental extremes with a de |
| Long Description       | Buchanan, Wire Connector, B-CAP, Conductor Range: 22 - 8 AWG, 2/18 AWG Min, 5/12 AWG Max, Number Of Conductors: 2 to 6, Material: Flame-retardant Polypropelene, Color: Red, Voltage Rating: 600 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: B2  |
| Product Type           | B-Cap B2 Red, 350 Jar   |
| Special Features       | 1,000V Maximum In Fixtures And Signs;Deep Skirt Protects Against Flash-Over And Turned-Back Strands For Maximum Dielectric Protection;Easily Removed For Repeat Usage On Same Size Or Larger Wire Combinations;Features: Classic Fin Design Provides Secure Grip For Extra Leverage On Maximum Wire Combinations;Green-B Designed For Making Ground Connections And Bonding Non-Metallic Sheathed Cable;Live-Action Spring Expands To Accept Wire Shape And Size No Pre-Twisting Required;Model Number: B2;Square-Wire Spring T |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Buchanan       |
| GTIN                      | 00781789452005 |
| Manufacturers Part Number | B2-350JR       |
| UPC                       | 781789452005   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
|----------------------|--|

## Availability

|             |     |
|-------------|-----|
| minimum qty | 350 |
|-------------|-----|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 350  |
| Package         | 2100 |
| Weight Per each | 0    |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

|                          |  |
|--------------------------|--|
| Application              | Insulating or Joining 1 or more conductors                       |
| environmental conditions | Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F) |
| standard                 | CSA C22.2 #188, UL 486C Listed, RoHS                             |