


Eaton BA43A

Catalog Number: BA43A

NEMA A200 Thermal Overload Relay, Three-pole, Starter mounted, NEMA , Thermal Type B, Class 20, 1NC Auxiliary Contact, Ambient Compensated , Full load range 19-135A

General specifications



Product Name

Eaton Freedom NEMA overload relay

Catalog Number

BA43A

UPC

786678003238

Product Length/Depth

8.2 in

Product Height

5.1 in

Product Width

6 in

Product Weight

2.1 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

CSA Certified

Catalog Notes

Replacement for Type A Overload Relays in Manual Reset Mode (3-Pole Only). Includes contactor mounting bracket, overload relay and connection straps to contactor.

Modification

1NC Auxiliary Contact, Ambient Compensated

Design

NEMA

Full load current range

19-135A

Mounting

Starter

Number Of Poles

Three-pole

Special features

Heaters required

Trip Type

Thermal Type B, Class 20

Type

A200

Catalogs

Eaton's Volume 5—Motor Control and Protection

Installation instructions

Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers

Specifications and datasheets

Eaton Specification Sheet - BA43A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia