

# Eaton BAB2050

Catalog Number: BAB2050

Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,Bolt-on mounting, High intensity discharge,50 A,10 kAIC,Two-pole,120/240 V,Non-Interchangeable,Q7,BAB

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BAB thermal magnetic circuit breaker	BAB2050
	UPC
	786679302507
<b>Product Length/Depth</b>	<b>Product Height</b>
3.8 in	4.8 in
<b>Product Width</b>	<b>Product Weight</b>
2.2 in	0.65 lb
<b>Warranty</b>	<b>Certifications</b>
1 year	UL Listed
	CSA Certified
<b>Catalog Notes</b>	
HACR rated	



## Physical Attributes

### Circuit breaker type

BAB

### Number of poles

Two-pole

### Type

Quicklag industrial thermal-magnetic circuit breaker

## Performance Ratings

### Amperage Rating

50 A

### Interrupt rating

10 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

120/240 V

## Miscellaneous

### Quantity

7

### Special features

Bolt-on mounting

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 4—Circuit Protection](#)

### Multimedia

[Circuit Breakers Explained](#)

### Specifications and datasheets

[Eaton Specification Sheet - BAB2050](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)