

Eaton BAB3030H

Catalog Number: BAB3030H

Eaton Quicklag industrial thermal-magnetic circuit breaker, 30A, BAB type, 10 kAIC, Bolt-on mounting, Three-pole, Non-Interchangeable, 240V

General specifications



Product Name	Catalog Number
Eaton BAB thermal magnetic circuit breaker	BAB3030H
	UPC
	786679303306
Product Length/Depth	Product Height
3.3 in	2.9 in
Product Width	Product Weight
2.9 in	0.95 lb
Certifications	Catalog Notes
UL Listed	HACR rated
CSA Certified	

Physical Attributes

Circuit breaker type

BAB

Mounting Method

Bolt-on

Number of poles

Three-pole

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

30 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

Miscellaneous

Special features

Bolt-on mounting

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - BAB3030H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)