

Eaton BAB3060H

Catalog Number: BAB3060H

Eaton BAB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,60 A,10 kAIC,Three-pole,240 V,Interchangeable,BAB,Distribution panels 240V (Three-phase, four-wire maximum),Four-wire,Three-phase



General specifications

Product Name	Catalog Number
Eaton BAB thermal magnetic circuit breaker	BAB3060H
	UPC
	786679303603
Product Length/Depth	Product Height
3.8 in	4.7 in
Product Width	Product Weight
3.2 in	0.95 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified
Catalog Notes	
HACR rated	

Physical Attributes

Circuit breaker type

BAB

Number of poles

Three-pole

Number of wires

4

Type

Quicklag industrial thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

60 A

Interrupt rating

10 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

Miscellaneous

Special features

Bolt-on mounting

Used with

Distribution panels 240 V (Three-phase, four-wire maximum)

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Multimedia

[Circuit Breakers Explained](#)

Specifications and datasheets

[Eaton Specification Sheet - BAB3060H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)