



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAF10 10A 250V 13/32X1-1/2 Fa Midget Fuse

Bussmann Fuses

Catalog Number	BAF10
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series Baf Fuse, Fast Acting, 10 A, Non-Indicating, Ferrule End X Ferrule End, 200 Aic At 250 Vac, 10 Kaic At 125 Vac, Nickel-Plated Brass Endcaps, Standard, 250 V
Weight per unit	0.0100 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	10 Amp
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	1.5000 IN X 0.4100 IN X 0.4100 IN
interrupt rating	200 Amp at 250 Vac, 10000 Amp at 125 Vac
Material	Nickel-plated brass endcaps
media	Yes
Voltage Rating	250 VAC

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

Descriptions

Description	10A 250V 13/32X1-1/2 FA MIDGET FUSE
extra long description	BUSS BAF-10 BUSS MIDGET FUSE
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series BAF fuse, Fast acting, 10 A, Non-indicating, Ferrule end x ferrule end, 200 AIC at 250 Vac, 10 kAIC at 125 Vac, Nickel-plated brass endcaps, Standard, 250 V
Product Type	Buss Midget Fuse
Special Features	Nickel Plated Brass Endcap

Manufacturer Information

Brand	Eaton
GTIN	00051712320108
Manufacturers Part Number	BAF-10
UPC	051712320108

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Weight Per each	0.01

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	CE Marked