

Eaton BAF-10

Catalog Number: BAF-10

Eaton Bussmann series BAF fuse, Fast acting, 10 A, Non-indicating, Ferrule end x ferrule end, 200 AIC at 250 Vac|10 kAIC at 125 Vac, Nickel-plated brass endcaps, Standard, 250 V

General specifications



Product Name	Catalog Number
Eaton Bussmann series BAF fuse	BAF-10
UPC	Product Length/Depth
051712320108	1.5 in
Product Height	Product Width
0.41 in	0.41 in
Product Weight	Warranty
0.25 lb	Not Applicable
Compliances	
CE Marked	

Electrical rating

Amperage Rating

10 A

Interrupt rating

200 AIC at 250 Vac

10 kAIC at 125 Vac

Voltage rating

250 V

Physical details

Material

Nickel-plated brass endcaps

Packaging type

Standard

General information

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Replacement for "F15B" fuses

Resources

Catalogs

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - BAF-10](#)

Technical data sheets

[BAF-10-BUSS MIDGET FUSE](#)

Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)