



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BGRB B-Cap Wire Connector, BGR Green Grounding, 250/Box

Ideal

Catalog Number	BGRB
Manufacturer	Ideal
Description	Wire Connector, (2) #14 Awg Conductor Size, (5) #12 Awg Conductor Size, Green Insulation Color, +221 °F Operating Temperature, 2 to 5 Conductors, 0.01 LB
Weight per unit	0.0070 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant Polypropelene
----------	-------------------------------

Material, Color, and Finish

Color	Green
-------	-------

Descriptions

Description	B-CAP WIRE CONNECTOR,BGR GREEN GROUNDING, 250/BOX
extra long description	IDEAL BGR-B BGR GREEN GROUND, 250 B
Features	The B-CAP Wire Connector gets you in those hard-to reach spots comfortably, especially when you're retrofitting or updating. Slim, classic fins and an expanding interior spring give the B-CAP a secure grip with extra leverage, making it the most compact connector on the market for up to 5 #12 (Red Model B2).The unique, space-saving profile of the B-CAP makes it perfect for retrofit work and shallow boxes.The B-CAP also features a tough, flame-retardant shell that withstands environmental extremes with a de

Manufacturer Information

Brand	Buchanan
GTIN	00781789453675
UPC	781789453675

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
----------------------	----------------------------------------

Availability

minimum qty	250
Status	Inactive

Packaging

Carton	250
Weight Per each	0.007



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

environmental conditions

Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)

standard

CSA C22.2 #188, UL 467 Listed, RoHS