



| |
|----------------|
| Catalog Number |
| Notes |
| Type |

Contractor Select™

BarnGuard LED

Security Light

BarnGuard LED security lights combine a classic dayform with LED technology, ideal for upgrading the massive install base of mercury vapor or high pressure sodium (HPS) luminaires. The BarnGuard LED security lights feature high quality white light that makes them ideal for replacing the yellow light of HPS. And with up to 7,900 lumens there is enough light to replace up to 175W Mercury Vapor luminaires while saving up to 80% in energy costs. With an expected service life of over 10 years, the BarnGuard LED is a true maintenance-free solution.

FEATURES:

- Replace 175W Mercury Vapor lamps, with energy savings of up to 80%
- Combines a classic dayform with energy efficient LED technology. Payback within two years
- Built-in MVOLT (120V-277V) photo cell for dusk to dawn operation



| Catalog Number | UPC | Description | Replaces Up To | Lumens | Wattage | Voltage | CCT | Finish | Pallet qty. |
|------------------------------|--------------|----------------|--------------------|--------|---------|-----------|-------|--------|-------------|
| BGR LED P1 40K MVOLT PER/DNA | 194994252542 | Security Light | 175W Mercury Vapor | 4,700 | 36W | 120V-277V | 4000K | GREY | 96 |
| BGR LED P2 40K MVOLT PER/DNA | 194994252559 | Security Light | 175W Mercury Vapor | 7,900 | 56W | 120V-277V | 4000K | GREY | 96 |
| BGR LED P2 50K MVOLT PER/DNA | 194994252573 | Security Light | 175W Mercury Vapor | 7,900 | 56W | 120V-277V | 4000K | GREY | 96 |

More configurations are available [Click here](#) or visit www.acuitybrands.com and search for BGR LED.

| | |
|---|----------------|
| Accessories: Order as separate catalog number. | |
| ONA | Mounting Arm |
| CI Code | *136XUY |
| UPC Code | 00745973700907 |



| |
|----------------|
| Catalog Number |
| Notes |
| Type |

Contractor Select™

BarnGuard LED

Security Light

BarnGuard LED security lights combine a classic dayform with LED technology, ideal for upgrading the massive install base of mercury vapor or high pressure sodium (HPS) luminaires. The BarnGuard LED security lights feature high quality white light that makes them ideal for replacing the yellow light of HPS. And with up to 7,900 lumens there is enough light to replace up to 175W Mercury Vapor luminaires while saving up to 80% in energy costs. With an expected service life of over 10 years, the BarnGuard LED is a true maintenance-free solution.

FEATURES:

- Replace 175W Mercury Vapor lamps, with energy savings of up to 80%
- Combines a classic dayform with energy efficient LED technology. Payback within two years
- Built-in MVOLT (120V-277V) photo cell for dusk to dawn operation



| Catalog Number | UPC | Description | Replaces Up To | Lumens | Wattage | Voltage | CCT | Finish | Pallet qty. |
|------------------------------|--------------|----------------|--------------------|--------|---------|------------|-------|--------|-------------|
| BGR LED P1 40K MVOLT PER DNA | 194994252542 | Security Light | 175W Mercury Vapor | 4,700 | 36W | 120V -277V | 4000K | GREY | 96 |
| BGR LED P2 40K MVOLT PER DNA | 194994252559 | Security Light | 175W Mercury Vapor | 7,900 | 56W | 120V -277V | 4000K | GREY | 96 |
| BGR LED P2 50K MVOLT PER DNA | 194994252573 | Security Light | 175W Mercury Vapor | 7,900 | 56W | 120V -277V | 4000K | GREY | 96 |

More configurations are available [Click here](#) or visit www.acuitybrands.com and search for BGR LED.

| | |
|---|----------------|
| Accessories: Order as separate catalog number. | |
| ONA | Mounting Arm |
| CI Code | *136XUY |
| UPC Code | 00745973700907 |