



Catalog Number
Notes
Type

Contractor Select™

BarnGuard LED

Security Light

BarnGuard LED security lights combine a classic dayform with LED technology, ideal for upgrading the massive install base of mercury vapor or high pressure sodium (HPS) luminaires. The BarnGuard LED security lights feature high quality white light that makes them ideal for replacing the yellow light of HPS. And with up to 7,900 lumens there is enough light to replace up to 175W Mercury Vapor luminaires while saving up to 80% in energy costs. With an expected service life of over 10 years, the BarnGuard LED is a true maintenance-free solution.

FEATURES:

- Replace 175W Mercury Vapor lamps, with energy savings of up to 80%
- Combines a classic dayform with energy efficient LED technology. Payback within two years
- Built-in MVOLT (120V-277V) photo cell for dusk to dawn operation



Catalog Number	UPC	Description	Replaces Up To	Lumens	Wattage	Voltage	CCT	Finish	Pallet qty.
BGR LED P1 40K MVOLT PER DNA	194994252542	Security Light	175W Mercury Vapor	4,700	36W	120V -277V	4000K	GREY	96
BGR LED P2 40K MVOLT PER DNA	194994252559	Security Light	175W Mercury Vapor	7,900	56W	120V -277V	4000K	GREY	96
BGR LED P2 50K MVOLT PER DNA	194994252573	Security Light	175W Mercury Vapor	7,900	56W	120V -277V	4000K	GREY	96

More configurations are available [Click here](#) or visit www.acuitybrands.com and search for BGR LED.

Accessories: Order as separate catalog number.	
ONA	Mounting Arm
CI Code	*136XUY
UPC Code	00745973700907



Catalog Number
Notes
Type

Contractor Select™

BarnGuard LED

Security Light

BarnGuard LED security lights combine a classic dayform with LED technology, ideal for upgrading the massive install base of mercury vapor or high pressure sodium (HPS) luminaires. The BarnGuard LED security lights feature high quality white light that makes them ideal for replacing the yellow light of HPS. And with up to 7,900 lumens there is enough light to replace up to 175W Mercury Vapor luminaires while saving up to 80% in energy costs. With an expected service life of over 10 years, the BarnGuard LED is a true maintenance-free solution.

FEATURES:

- Replace 175W Mercury Vapor lamps, with energy savings of up to 80%
- Combines a classic dayform with energy efficient LED technology. Payback within two years
- Built-in MVOLT (120V-277V) photo cell for dusk to dawn operation



Catalog Number	UPC	Description	Replaces Up To	Lumens	Wattage	Voltage	CCT	Finish	Pallet qty.
BGR LED P1 40K MVOLT PER/DNA	194994252542	Security Light	175W Mercury Vapor	4,700	36W	120V-277V	4000K	GREY	96
BGR LED P2 40K MVOLT PER/DNA	194994252559	Security Light	175W Mercury Vapor	7,900	56W	120V-277V	4000K	GREY	96
BGR LED P2 50K MVOLT PER/DNA	194994252573	Security Light	175W Mercury Vapor	7,900	56W	120V-277V	4000K	GREY	96

More configurations are available [Click here](#) or visit www.acuitybrands.com and search for BGR LED.

Accessories: Order as separate catalog number.	
ONA	Mounting Arm
CI Code	*136XUY
UPC Code	00745973700907