

Specifications

Eaton BJ94



Photo is representative

Eaton Crouse-Hinds series XJG bonding jumper, Rigid/IMC, 4" maximum conduit movement, Used with XJG94 HDG, 3-1/2" trade size

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG bonding jumper
CATALOG NUMBER	BJ94
UPC	782274992006
PRODUCT LENGTH/DEPTH	30 in
PRODUCT HEIGHT	0.88 in
PRODUCT WIDTH	0.19 in
PRODUCT WEIGHT	3.2 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

CONDUIT TYPE	Rigid/IMC
TRADE SIZE	3-1/2"
CONDUIT MOVEMENT - MAX	4"
SPECIAL FEATURES	Used with XJG94 HDG

Resources

BROCHURES	Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure
CATALOGS	Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page
CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BJ94 Expansion and Deflection Couplings

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

